

## HS Hybrid Digital Video Recorder with Looping Outputs and Real-Time Recording

**D8HS** 8 Channel IP & Analog Hybrid DVR

**D16HS** 16 Channel IP & Analog Hybrid DVR

**Storage** 1TB – 12TB

D8HS1TB	D8HS6TB	D16HS1TB	D16HS6TB
D8HS2TB	D8HS8TB	D16HS2TB	D16HS8TB
D8HS3TB	D8HS9TB	D16HS3TB	D16HS9TB
D8HS4TB	D8HS12TB	D16HS4TB	D16HS12TB




Front panel



Rear panel

D8HS shown

15" (W) x 13.4" (D)



2.83" (H)

### Features

#### EZ Wizards

- Camera: quickly discovers and installs IP cameras
- Setup: for quick system setup
- Network: network setup and portforwarding
- Record: quickly setup recording resolutions and recording type

**EZ Search:** quickly search events from thumbnails

**EZ Copy:** auto copy what you are playing onto a USB flash drive

- Video Out: 1 HDMI®, 1 VGA, 1 CVBS, 1 Spot
- Real-time recording rate at 30fps/channel for analog channels at 960H and IP channels at Full HD (1920x1080)
- Up to 5MP resolution on channel 1
- Plug & play feature with Speco's OnSIP/VIP/ZIP cameras
- ONVIF support\*
- Dual network ports for isolating IP camera network and remote network traffic
- Each channel is configurable for either IP or analog
- H.264 video compression
- Networkable hybrid DVR with free Speco DDNS server
- Digital Deterrent® for triggering audio message via motion detection or sensor
- 2-way audio communication
- Programmable recording on motion detection, sensor, schedule, continuous and manual
- Supports wireless access point for viewing and configuration

- Built-in S.M.A.R.T. Technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Switch between low and high quality stream during simultaneous Continuous + Motion or Continuous + Sensor recording modes for storage optimization
- Easy firmware upgrade by USB port or network
- User Access: up to 4 concurrent users
- Remote monitoring / recording / playback / configuration / software upgrades and PTZ control via internet
- Network software supports Static IP, DHCP and DDNS
- Network accessible via SpecoTech Multi-Client Software, SecureGuard™ Plus CMS, Internet Explorer Web-Viewer and Speco Player Mobile Viewer
- PC and MAC® compatible
- IR remote control & mouse included
- Rack mountable (hardware included)
- 3 year warranty

### Optional Accessories



**ERS1V**  
Vented Rack Shelf



**IRRPTKIT**  
IR Repeater Kit



**DSWFUSB**  
USB Wireless  
Access Point



**POE4SW5**  
4 PoE Port 10/100  
802.3af/ at Switches



**POE8SW9**  
8 PoE Port 10/100  
802.3af/ at Switches



**POE16SW18**  
16 PoE Port 10/100  
802.3af/ at Switches

Free Apps with support for view on most smart devices \*Visit [www.specotech.com/onvif.html](http://www.specotech.com/onvif.html) for latest ONVIF support. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 7/31/15





## Technical Specifications:

### HS Hybrid Digital Video Recorder with Looping Outputs and Real-Time Recording

Model			D8HS	D16HS	
Video	Input	IP Channels	Up to 8	Up to 16	
		Analog Channels	Up to 8	Up to 16	
	Output	HDMI®	1 HDMI (1280x720 / 1920x1080)		
		VGA	1 VGA (1280x720 / 1920x1080)		
		CVBS	1		
		SPOT	1 (Analog channels only)		
Loopouts	8 (Analog channels only)	16 (Analog channels only)			
Audio	Input		8 line input, 8 IP input	16 line input, 16 IP input	
	Output	Local Output (RCA)	1	1	
	Audio Codec		G.711		
Alarm	Sensor Input	Local Input	4	4	
		Remote Input from IP Camera	8	16	
	Alarm Output		1	1	
Serial	RS-232C	Debugging Only	1		
	RS-485	PTZ	1		
Recording	Compression		1 H.264 (baseline, main, high profile)		
	Resolution	IP	2592x1944 (5MP)	Channel 1	
			1920x1080 (1080p)	240fps	480fps
			1280x720 (720p)	240fps	480fps
		Analog	960H	240fps	480fps
			D1	240fps	480fps
			CIF	240fps	480fps
	Recording Quality Grade (Analog Only)		5 levels		
	Recording Mode		Continuous / Motion / Sensor / Schedule / Manual / Continuous + Sensor / Continuous + Motion		
	Pre-Recording		Max. 20 minutes		
Post Recording		Max. 60 seconds			
Playback	Search		EZ Search, Date/Time, Event, Archive, Log		
	Multi-Decoding		1, 4, 8	1, 4, 9, 16	
	Playback Speed		x0.25, x0.5, x2, x4, x8, x16, x32, x64		
Backup	Media		USB Drive, External HDD, Network		
	Format		BMP, AVI, Proprietary Format		
	Large Backup		Yes (max. 24 hours)		
Storage	HDD	Capacity of 1 HDD	4TB		
		Internal HDDs	3		
		e-SATA	1		
	USB		2 front, 1 rear		
User I/F	Menu Display		GUI		
	Input Method		Front Buttons, IR, Mouse, Keyboard Controller		
Network	Interface		Dual Network Ports 10/100/1000Base-T		
	Streaming	IP Channel	Depends on profile		
		Analog Channel	CIF @ 30fps/channel		
	Dual Encoding for Network		Yes		
Max. Throughput		40Mbps			
Network Access	Mobile Viewer		Speco Player (Live, Search, PTZ, 2-Way Audio)		
	PC Web Viewer		IE, Chrome, Firefox, Safari (Live, Search, Backup, PTZ, Remote Setup)		
	PC Client		SpecoTech Multi-Client Viewer and SecureGuard® CMS		
Features	Digital Deterrent®		Default + up to 8 audio files		
	Digital Zoom		Yes		
	DLS (Daylight Savings)		Yes		
	EZ Record		Yes		
	S.M.A.R.T		Yes		
	Internal Beep		Yes		
	Multi-Language		Yes		
	Dynamic DNS		Yes (free Speco DDNS)		
	SW Upgrade		USB and remote software upgrade		
	E-mail Notification		Yes		
NTP (Network Time Protocol)		Yes			
Power Source	Power Supply Voltage		12VDC, 5A		
Allowable Operating Temperature / Humidity			41° F - 104° F / 20% - 80% RH (non-condensing)		
Allowable Storage Temperature			14° F - 122° F		
Weight	Unit Weight (Gross Weight)		12 lbs.		
Dimensions	Unit Dimensions (W x H x D)		15" (W) x 2.83" (H) x 13.4" (D)		

Please note that specifications and unit exterior design are subject to change without notification.