

25U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

StarTech ID: 4POSTRACK25U



The 4POSTRACK25U 25U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 25U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment..

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

Features

- 25U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

Technical Specifications

Warranty	2 Years
Rack Type	4-Post
Casters	Included
U Height	25U
Frame Type	Open Frame
Front Door Type	Open
Key Lock	No
Industry Standards	DIN 41494
Industry Standards	EIA/ECA-310-E
Industry Standards	IEC 60297-3-100
Fan(s)	No
Weight Capacity	1202.9 lb [544.3 kg]
Color	Black
Enclosure Type	Steel
Internal Width	18.3 in [465 mm]
Internal Height	43.9 in [1115.8 mm]
External Width	23.6 in [600 mm]
External Height	47.8 in [1215.3 mm]
External Depth	26.1 in [661.8 mm]
Product Weight	44.2 lb [20 kg]
Maximum Mounting Depth	40 in [1016 mm]
Minimum Mounting Depth	22 in [558.8 mm]
Height with Casters	50.8 in [1290 mm]
Shipping (Package) Weight	48.6 lb [22 kg]
Included in Package	2 - Left Vertical Rail
Included in Package	2 - Right Vertical Rail
Included in Package	2 - Base Bracket
Included in Package	8 - Corner Section
Included in Package	4 - Center Section
Included in Package	2 - Top Bracket
Included in Package	48 - M8 Bolt
Included in Package	48 - M8 Washer
Included in Package	1 - M8 (13mm) Wrench
Included in Package	1 - M6 (10mm) Wrench

Included in Package	1 - Phillips Screwdriver
Included in Package	32 - M6 Cage Nut
Included in Package	32 - PVC Cup Washer
Included in Package	32 - M6 Phillips Head Screw
Included in Package	12 - Cable Management Hook
Included in Package	12 - Hook Mounting Screw
Included in Package	4 - Casters
Included in Package	4 - Leveling Feet
Included in Package	16 - M6 Screw
Included in Package	16 - M6 Flat Washer
Included in Package	16 - M6 Flange Nut
Included in Package	4 - Grounding Wires

Certifications, Reports and Compatibility

