

HSM SECURIO B35

Document shredder

Ideal for open-plan offices



- Integrated light barrier starts shredder automatically and switches it off after paper feed ends
- Anti-Jam Technology prevents jams when machine is overloaded
- Continuous Duty operation ensures continual shredding with no down time
- High user safety guaranteed by the folding safety element which prevents unintentional intake
- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Comprehensive safety system - UL Approved, CE-certified
- Cutting cylinder made of 100% solid steel for high cutting capacities
- Separate reverse button
- LED indicates machine status, container full, cutting unit blocked and door open
- Inspection window to monitor filling level
- Casters for mobility and shared use
- Optional Automatic external oiler for cross cut, micro cut and HS P-6 ensures long time cutting performance and quality
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1920	HSM1921	HSM1923	HSM1922	HSM1925
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut	HS P-6
Cutting size	1/8"	1/4"	3/16" x 1 1/8"	1/16" x 9/16"	1/32" x 7/16"
Security level DIN 32757-1	2	2	3	4	5
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2	P-6 / F-3
Cutting capacity per run in sheets	30 - 32	40 - 42	24 - 26	16 - 18	10
Cutting speed	17 ft / min	17 ft / min	15.75 ft / min	15.75 ft / min	15.75ft / min
Throat opening	15.75"	15.75"	15.75"	15.75"	15.75"
Motor power (hp)	0.79	0.79	0.79	0.87	0.79
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"
Weight	106.5 lbs	106.5 lbs	120 lbs	120 lbs	120 lbs
Shred-bin volume	34.3 gallons	34.3 gallons	34.3 gallons	34.3 gallons	34.3 gallons
Cutting capabilities					

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service / 800.613.2110