
MMR SERIES RACK, 18 RU, 24"D

MMR-1824 |



FEATURES & BENEFITS

The Essex Multi Mount Rack is a fully-welded equipment mounting solution offering exceptional versatility at an affordable price. MMR Series racks feature the flexibility to be installed desktop, floor-standing or wall mounted in one of three distinct ways.



PRODUCT
ENVIRONMENTAL PROFILE

- Most versatile fully welded rack that can be desktop, floor-standing or wall mounted
- Multiple wall mount options provide flexibility for budgets and workflows: easy access pivot, hang bracket for mounting fully integrated rack, direct-to-wall
- Trusted Middle Atlantic quality
- Best value for entry-level AV systems
- Available in sizes complementary to residential AV systems: 10, 12, 16, 18, rackspaces
- UL Listed
- Up to 250 lb weight capacity
- Attractive design with sleek metallic grey finish
- Passive ventilation designed into rack top and sides; optional quiet DC fan tops move up to 276 CFM
- Options include casters for mobility, leveling feet for fixed installation, locking solid and plexi doors that install in seconds, minimizing installation time and accessory and power kits/bundles
- Ideal for installation in closets, basements and equipment rooms
- Front and rear rail options, fully adjustable

SPECIFICATIONS

GENERAL INFO

Finish: Metallic Grey
UL Standards Tested: UL2416

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Listing No: E313734

DIMENSIONS

Usable Depth: 22
Usable Height: 31.5
Panel Width: 19
Capacity Weight (US): 250
Depth (US): 24
Height (US): 36.35
Width (US): 23.51
Rack Units: 18

TECHNICAL INFORMATION

Rackrail Type: 10-32
UL Load Capacity: 250
Mounting: Horizontal