

FHD 1080p

LED

ECONOMY WIDE LED BLU



1080p
Full HD

LED
Back Light

250cd/m²
Brightness

1000:1
Contrast

16.7
MILLION
Display Color

170°/160°
Viewing Angle

16:9
Aspect Ratio

22RCE


BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

OVERVIEW

The ORION Images Wide LCD w/ LED BLU (backlight unit) high brightness displays are a truly professional experience in next generation technology using eco-friendly material (no mercury or halogen). This unit applies standby mode (less than 1W) to save energy.

FEATURES

- 1920 x 1080p Full HD Maximum Resolution
- LED BLU (Back Light Unit) Display Monitor
- 250cd/m² High Brightness / 1000:1 Contrast Ratio
- 3D Comb Filter
- 16 : 9 Wide Aspect Ratio
- 170° / 160° Viewing Angle
- BNC Video 2 In, BNC Video 1 Out, HDMI 1 In, VGA 1 In, Audio 1 In, Audio 1 Out, Internal Speaker
- Optional Wall and Ceiling Mount Kits




**24
7
365**
Built to run 24 x 7 x 365
Continuously

SPECIFICATIONS


22RCE	
Display	
Screen Size	21.5 Inch
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.2482 x 0.2482mm
Brightness	250cd/m ²
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	170° / 160°
Display Color	16.7 Million
Response Time	< 5ms
Video System	NTSC / PAL
Interface	
Video In (BNC Type)	2 In
Video Out (BNC Type)	1 Out
HDMI In	1 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	1 In
Audio Out (RCA Type)	1 Out
Transmitter	
Remote Control	Yes
Audio	
Built-in Speakers	Yes (2W x 2)
Features	
Filter Type	3D Comb Filter
Multi Language	English, Chinese
General	
Outline Dimension (W x H x D)	20.12" x 12.28" x 1.69" (w/o stand)
Net Weight	6.6 lbs (w/ stand)
Material / Color	Plastic / Black
Desk Top Stand	Yes
Part / Labor	2year / 2year
Power	DC 12V / 3A, Less then 30W
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	100mm (2 holes)
Wall	WB-5, WB-10, WB-30, WB-31
Ceiling	CMK-01

*Design and specifications are subject to change without notice

INPUT INTERFACE



DIMENSIONS



FEATURE

Scan Size can be selected as AUTO / 16 : 9 / 4 : 3 / Panorama / Zoom



OPTIONAL MOUNTS

