

**FHD 1080p**

**LED**

**ECONOMY WIDE LED BLU**



**1080p**  
Full HD

**LED**  
Back Light

**250cd/m<sup>2</sup>**  
Brightness

**1000:1**  
Contrast

**16.7 MILLION**  
Display Color

**170°/160°**  
Viewing Angle

**16:9**  
Aspect Ratio

# 24RCE

BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

## OVERVIEW

The ORION Images Wide LCD w/ LED BLU (backlight unit) high brightness displays are a truly professional experience in next generation technology using eco-friendly material (no mercury or halogen). This unit applies standby mode (less than 1W) to save energy.

## FEATURES

- » 1920 x 1080p Full HD Maximum Resolution
- » LED BLU (Back Light Unit) Display Monitor
- » 250cd/m<sup>2</sup> High Brightness / 1000:1 Contrast Ratio
- » 3D Comb Filter
- » 16 : 9 Wide Aspect Ratio
- » 170° / 160° Viewing Angle
- » BNC Video 2 In, BNC Video 1 Out, HDMI 1 In, VGA 1 In, Audio 1 In, Audio 1 Out, Internal Speaker
- » Optional Wall and Ceiling Mount Kits




### SPECIFICATIONS


24RCE	
<b>Display</b>	
Screen Size	23.6 Inch
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.2715 x 0.2715mm
Brightness	250cd/m <sup>2</sup>
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	170° / 160°
Display Color	16.7 Million
Response Time	< 5ms
Video System	NTSC / PAL
<b>Interface</b>	
Video In (BNC Type)	2 In
Video Out (BNC Type)	1 Out
HDMI In	1 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	1 In
Audio Out (RCA Type)	1 Out
<b>Transmitter</b>	
Remote Control	Yes
<b>Audio</b>	
Built-in Speakers	Yes (2W x 2)
<b>Features</b>	
Filter Type	3D Comb Filter
Multi Language	English, Chinese
<b>General</b>	
Outline Dimension (W x H x D)	21.16" x 13.46" x 2.03" (w/o stand)
Net Weight	7.7 lbs (w/ stand)
Material / Color	Plastic / Black
Desk Top Stand	Yes
Part / Labor	2year / 2year
Power	DC 12V / 3A, Less then 30W
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
<b>Mounts</b>	
VESA™ Mount Size	75 x 75mm
Wall	WB-5, WB-10, WB-30, WB-31
Ceiling	CMK-01

\*Design and specifications are subject to change without notice

### INPUT INTERFACE



### DIMENSIONS



### FEATURE

Scan Size can be selected as AUTO / 16 : 9 / 4 : 3 / Panorama / Zoom



### OPTIONAL MOUNTS

