



IP NETWORK MONITOR



FULL HD 1080p

LED



32IREDP

BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

OVERVIEW

The ORION Images released a new 32 inch network CCTV monitor with built-in Android 4.2 OS, Quad Core RK 3188, Cortex A9, 8GB internal memory and snap shot* capability.

FEATURES

- WiFi 802.11b/g/n Wireless
- Support RJ45, 10/100M LAN Network
- LED BLU (Back Light Unit) Display Monitor
- PIP / PBP Multi Display Function
- 3D Comb Filter / Deinterlace, Noise Reduction, Advanced Auto Power Recovery, Auto Pixel Shift, Auto Source Sequencing, Trigger Source Switching, Multi-Language Support
- Ethernet 1 In, WiFi, USB 2 In, BNC Video 2 In / 2 Out, S-Video 1 In / 1 Out, VGA 1 In, DVI-D 1 In, HDMI 2 In, Audio 2 In, PC Stereo 1 In
- Built-In Speakers
- Wall and Ceiling Mounts
- 1920 x 1080p Full HD
- Metal Chassis

* Snap Shot feature is based on application support



Industrial



Interface



Slim




Built to run 24 x 7 x 365
Continuously

SPECIFICATIONS

32IREDP	
Display	
Screen Size	31.55 Inch
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.36375 x 0.36375mm
Brightness	400cd/m²
Contrast Ratio	1300 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	16.7 Million
Response Time	< 8ms
Video System	NTSC / PAL
Interface	
RJ45	Built-In Android 4.2 OS, Quad Core RK3188, Cortex A9, 8GB Internal Memory WiFi 802.11b/g/n
Video In / Out (BNC Type)	2 In / 2 Out
S-Video In / Out	1 In / 1 Out
DVI-D In / HDMI In	1 In / 2 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	2 Left & Right
PC Stereo In	1 In
Transmitter	
Remote Control	Yes
Audio	
Built-in Speakers	Yes (1W x 2)
Features	
Multi Display Function	PIP / PBP
Filter Type	3D Comb Filter
Deinterlacing	Yes
Noise Reduction Control (NR)	Yes
Advanced Auto Power Recovery	Yes
Auto Pixel Shift	Yes
Auto Source Sequencing	Yes
Trigger Sensor	Yes (NO / NC)
Multi Language	English, Spanish, French, German, Italian
General	
Outline Dimension (W x H x D)	28.82" x 18.98" x 5.91" (w/ stand)
Net Weight	8.5 Kg (18.74 lbs)
Material / Color	Metal / Black
Desk Top Stand	Yes
Part / Labor	3year / 3year
Consumption: < On	< 67W
	AC100 ~ 240V(50/60Hz)
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	200 x 200mm
Wall	WB-31, WB-2642
Ceiling	CMK-01

*Design and specifications are subject to change without notice


INPUT INTERFACE



- | | |
|-------------------------|---------------------|
| 1 Ethernet | 8 Audio 2 In / Out |
| 2 USB In 1 & 2 | 9 S-Video In / Out |
| 3 HDMI In 1 & 2 | 10 Video 1 In / Out |
| 4 DVI-D In | 11 Video 2 In / Out |
| 5 VGA (15 Pin D-Sub) In | 12 Trigger In |
| 6 PC Stereo In | 13 AC Power |
| 7 Audio 1 In / Out | |



DIMENSIONS



ADVANTAGES

IP NETWORK CONNECTION



- 3 Use 32IREDP as desktop PC monitor

