

WorkForce WF-100W

DATASHEET



This is the portable printer you've been waiting for. Epson's first-ever A4 portable printer is great for professionals who need to print invoices, contracts and more while working remotely. Small and light, this inkjet printer features an integrated battery, an LCD screen, Wi-Fi and Wi-Fi Direct® connectivity, and compatibility with Apple AirPrint², Google Cloud Print and Epson iPrint³.

Portable printing

The world's smallest and lightest A4 inkjet printer¹, the WF-100W has a built-in battery that can be recharged anywhere via USB. It's small and compact, measuring just 309x154x61mm and weighing 1.6kg. Its wireless connectivity means the WF-100W cuts out all cables, allowing it to be used hassle-free both in clients' homes or in a vehicle.

Convenient

Compatible with Apple AirPrint² and Google Cloud Print for wireless printing, the WF-100W also benefits from Epson Connect. As well as the Epson iPrint³ app for wireless printing from most tablets or smartphones, Epson Connect also includes Email Print, which means you can print from anywhere in the world³.

High quality

The quality of this printer is reflected in the quality of the printouts. In fact, it is the only portable printer that uses pigment inks, for durable, smudge-free results.

Efficient

The WF-100W delivers an ISO print speed of 7ppm in black and 4ppm in colour⁴ and has an ink yield of up to 250 pages in black and 200 in colour⁵. The only portable printer with an LCD screen¹, it's always easy to set-up a Wi-Fi connection without the need for a PC, and to check ink supply levels.

KEY FEATURES

- **Portable printing**
Lightweight, compact design
- **Rechargeable battery**
Plug into any USB port or recharge with the bundled AC adaptor
- **Wi-Fi & Wi-Fi Direct**
Print wirelessly wherever you are
- **Quality results**
Pigment inks ensure top results
- **User-friendly**
Hassle-free with simple set-up



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	3 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment ink
Nozzle Configuration	180 Nozzles black, 59 Nozzles per colour
Category	Office
All-in-One Functions	Print

PRINT

Printing Speed ISO/IEC 24734 7 Pages/min Monochrome, 4 Pages/min Color

Printing Speed ISO/IEC 24734 4 Pages/min Monochrome, 2 Pages/min Colour

(battery operated)

Maximum Printing Speed 14 Pages/min Monochrome (plain paper), 11 Pages/min Color (plain paper)

Printing Resolution 5.760 x 1.440 dpi

Colours Black, Colour

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

PAPER / MEDIA HANDLING

Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter Legal, 10 x 15 cm, 13 x 18 cm
Duplex	No
Paper Tray Capacity	20 Sheets Standard, 20 Sheets maximum, 5 Photo Sheets
Number of paper trays	1
Compatible Paper Weight	300 g/m²

CONNECTIVITY

Interfaces	USB 2.0 Type Mini-B, Wireless LAN IEEE 802.11b/g/n, Wi-Fi Direct
Network Printing Protocols	IPP, LDP, Port 9100, WSD
Network Management	SNMP, HTTP, DHCP, APIPA, DDNS, mDNS, Ping, SLP, WSD, LLTD
Protocols	
Mobile and Cloud printing services	Epson Connect (iPrint, Email Print, Remote Print Driver), Apple AirPrint, Google Cloud Print
Network Protocols	TCP/IPv4, TCP/IPv6

GENERAL

Energy Use	1,3 W (sleep mode), 11 W (printing), 4 W (Ready), 0,3 W (Power off), ENERGY STAR® qualified
Product dimensions	309 x 154 x 61 mm (Width x Depth x Height)
Product weight	1,6 kg
Noise Level	45 dB (A) according to ISO 9296
Compatible Operating Systems	Mac OS 10.7.x, Mac OS 10.8.x, Mac OS 10.9.x, Mac OS X 10.6.8, Windows 7, Windows 7 x64, Windows 8 (32/64 bit), Windows 8.1, Windows 8.1 x64 Edition, Windows Server 2003 (32/64bit), Windows Server 2008 (32/64bit), Windows Server 2008 R2, Windows Server 2012 (64bit), Windows Server 2012 R2, Windows Vista, Windows Vista x64, Windows server 2003 R2
Supply Voltage	AC 100 V - 240 V, 50 Hz - 60 Hz
Power Supply	100V, 110V, 220V, 240V
Battery type	integrated

LOGISTICS INFORMATION

SKU	C11CE05402
EAN code	8715946540313
Dimensions Single Carton	384 x 130 x 260 mm
Carton Weight	2,1 Kg
Multiple Order Quantity	1 Units
Country of Origin	Indonesia
Pallet Size Euro	144 Units

Epson Deutschland GmbH
Otto-Hahn-Str. 4
D-40670 Meerbusch
Info-Line: 02159 92 79 500
Telefax: +49 (0) 2159/538-3000
www.epson.de

Epson in Österreich
Info-Line: 01 253 49 78 333
www.epson.at
Epson in der Schweiz
Info-Line: 022 592 7923
www.epson.ch

Alle Marken und eingetragenen Warenzeichen sind das Eigentum der Seiko Epson Corporation oder der jeweiligen Rechteinhaber.
Diese Produktinformationen können ohne vorherige Ankündigung geändert werden.

WorkForce WF-100W

WHAT'S IN THE BOX

- AC Adaptor
- Main unit
- Mini-USB cable
- 2x Maintenance box
- Ink cartridges (1 black, 1 three-colour cartridge)

INK CARTRIDGE COMPATIBILITY

● 266



● 267



INK YIELD DATA



Globe 267

- 250 pages*
- 200 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Compared to A4 inkjet printers available in the market in August 2014. Product dimensions, weight and specifications as stated on manufacturers' websites 2. AirPrint-enabled printers work with iPad (all models), iPhone (3GS or later), and iPod touch (3rd generation or later) running the latest version of iOS. AirPrint and the AirPrint logo are trademarks of Apple Inc 3. Epson iPrint requires a wireless connection. Email print requires an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu 4. Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default simplex/duplex. For more information visit www.epson.eu/testing 5. Approx. page yield based on ISO/IEC 24711/24712. Actual yield will vary depending on images printed and usage conditions. For more information visit www.epson.eu/pageyield

EPSON®