



## H-IN4-F32

4-Input HDMI Card

| HDMI | HDCP Compliant | Kramer Core

---



H-IN4-F32 is a four-channel HDMI input card for the VS-3232D Modular Multi-Format Digital Matrix Switcher. The H-IN4-F32 inputs four HDMI signals to the chassis

### FEATURES

---

Max. Data Rate - 6.75Gbps (2.25Gbps per graphic channel)

HDCP 1.4 Compliant

HDMI 1.3a Compliant

3D Pass-Through



# KRAMER

## TECHNICAL SPECIFICATIONS

---

INPUTS:	4 HDMI
BANDWIDTH PER CHANNEL:	2.25Gbps
TOTAL BANDWIDTH:	6.75Gbps
MAXIMUM RANGE:	15m (49ft)
3D PASS THROUGH:	Supported
POWER CONSUMPTION:	9W
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F)
STORAGE TEMPERATURE:	-40° to +70°C (-40° to 158°F)
HUMIDITY:	10% to 90%, RHL non-condensing
STANDARD COMPLIANCE:	HDCP 1.4, HDMI 1.3a
SAFETY REGULATORY COMPLIANCE:	CE
ENVIRONMENTAL REGULATORY COMPLIANCE:	Complies with appropriate requirements of RoHs and WEEE