

USB 3.0 / eSATA 6-Bay Hard Drive Duplicator Dock - 1:5 HDD / SSD Cloner and Eraser

StarTech ID: SATDOCK5U3ER



The SATDOCK5U3ER Hard Drive Duplicator & Docking Station lets you clone a 2.5in or 3.5in SATA hard drive (HDD) or solid-state drive (SSD) to five other SATA drives simultaneously, as a standalone device. The duplicator also lets you erase up to 5 drives, without a host connection.

You can also use the duplicator as a 5-bay HDD / SSD docking station, by connecting it to a host computer system through either USB 3.0 or eSATA. With support for high-capacity drives (tested with up to 6TB), this is a simple and cost-effective way to boost your data storage/backup capabilities.

Optimized Productivity

By copying data from one drive to five drives simultaneously, the hard drive cloner helps boost your productivity by avoiding the hassle of repeatedly swapping drives in and out during high volume duplication projects.

Plus, the dock supports erasing up to five drives simultaneously with multiple operating modes, including Quick Erase as well as Multipass Overwriting (DoD) -- the ideal solution for permanently erasing confidential information and helping to protect your business and your clients from identity theft.

Hassle-free Performance

With a built-in LCD display, the SATDOCK5U3ER makes it easy to monitor duplication progress and review copy/erase results and drive diagnostics during standalone operation.

The housing has also been specifically designed with ease-of-use in mind. The drive slots feature a dual-profile design to support hassle-free swapping between 2.5in and 3.5in hard drives and solid-state drives without having to use additional brackets or adapters.

Maximum Versatility

With the option to connect the docking station through either eSATA or USB 3.0, the SATDOCK5U3ER provides a versatile solution for expanding the storage capability of almost any laptop or desktop computer. For fast performance, you can connect the docking station to your computer through eSATA for efficient data transfer speeds up to 3 Gbps. For broader system compatibility, you can connect the dock through USB 3.0, which is also backward compatible with USB 2.0/1.1 host connections.

The SATDOCK5U3ER also provides two charge-only, fast-charge USB ports, that you can use to keep your iPhone®, iPad®, and Android® tablets or smartphones charged.

You can also duplicate, erase or access other drive types in duplication and quick-erase applications using a drive adapter. The following StarTech.com adapters have been tested to ensure compatibility with this drive duplicator:

[2.5/3.5in IDE drives](#) - SAT2IDEADP

[mSATA drives](#) - SAT2MSAT25

[M.2 \(NGFF\) drives](#) - SAT32M225

Built for dependable, long-term performance the SATDOCK5U3ER is durably constructed and backed by a StarTech.com 2-year warranty and free lifetime technical support.

Toepassingen

- Create multiple exact replicas of a source drive onto a new drive for large deployment of identical computer systems
- Make exact copies of original hard drives for testing or investigation in law enforcement and forensic applications
- Quickly access external hard drives
- Clone data for disk recovery
- Securely erase multiple drives simultaneously to protect yourself against identity theft

Eigenschappen

- Save time with 1:5 mass drive duplication & 6-drive mass erasing
- Hassle-free standalone operation with built-in digital LCD display
- Maximize versatility with eSATA & USB 3.0 host connections, charge only USB fast-charge ports, plus docking station, eraser and duplicator in a single device
- Three modes of sector-by-sector drive duplication
- Erase up to five drives simultaneously with single-pass and multi-pass overwriting / DoD erasing
- eSATA and USB 3.0 host interface connections
- Supports 2.5in or 3.5in form factor hard drives (HDD) or solid-state drives (SSD)
- Supports SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives
- Compatible with USB 3.0/2.0/1.1 (5 Gbps / 480 Mbps / 1.5 Mbps)
- Built-in dual cooling fans with speed control

Technische specificaties

Warranty	2 Years
Number of Drives	5
Drive Size	2.5in / 3.5in
Compatible Drive Types (Type and Rate)	SATA
Fans	2 - 60 mm
Chipset ID	SunplusIT - SPIF260A ASMedia – ASM1453 JMicron – JMB393
Drive Connectors	6 - SATA Data & Power Combo (7+15 pin) Receptacle
Host Connectors	1 - eSATA (7 pin; Data) Receptacle
Host Connectors	1 - USB 3.0 B (9 pin; SuperSpeed) Female
Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
Type and Rate	SATA II (3 Gbps)
Port Multiplier	Yes
Max Drive Capacity	Currently tested with up to 6TB 7200 RPM
Product Length	315 mm [12.4 in]
Product Width	151.8 mm [6 in]
Product Height	75 mm [3 in]
Product Weight	1500 g [52.9 oz]
LED Indicators	1 - Docking station power
LED Indicators	1 - Source Drive Power and Activity
LED Indicators	5 - Target Drive Power / Activity
Power Source	AC Adapter Included
Input Voltage	100 ~ 240 AC
Input Current	2 A
Output Voltage	19 DC
Output Current	5 A
Center Tip Polarity	Positive
Operating Temperature	5°C to 35°C (41°F to 95°F)
Storage Temperature	-20°C to 50°C (-4°F to 122°F)
Humidity	20%~80% RH
Shipping (Package) Weight	2500 g [88.3 oz]
Included in Package	1 - USB 3.0\leSATA 1:5 SATA HDD Duplicator Dock
Included in Package	1 - USB 3.0 Cable
Included in Package	1 - eSATA Cable
Included in Package	4 - Rubber feet (installed)
Included in Package	1 - Universal Power Adapter (NA / UK / EU)

Included in Package

1 - Instruction Manual

Certificaten, rapporten en compatibiliteit

CE

FCC

 RoHS Compliant
Available