



Dell 27 Monitor P2715Q



Experience exceptional Ultra HD screen clarity for your next project, affordably

Exceptional screen performance

Enjoy monitor resolution that's closer to your camera's with over 8.3 megapixels on a large 27" Ultra HD screen.

- See 4 times more details than Full HD with Ultra HD 3840 x 2160 resolution.
- Work with consistent and accurate colors across an ultra-wide 178°/178° viewing angle.
- Get consistent and accurate colors right out-of-the-box with factory-tuned 99% sRGB color coverage at $\Delta E < 3$.
- View stunning color details with over 1.07 billion colors.

Flexible viewing and connectivity options

Work the way you like with a multitude of flexible viewing and connectivity options.

- Experience full adjustability with tilt, pivot, swivel and height adjustable features.
- Conveniently connect with smartphones, tablets, laptops and PCs through multiple input ports.
- Get outstanding image quality with content streamed via DisplayPort, mini-DisplayPort and HDMI (MHL) ports.
- Choose to wall mount your panel or attach it to the optional Dell Single Monitor Arm.
- Easily charge and power your BC1.2 devices with the high current USB 3.0⁷ charging port.

Reliable with an eco-conscious design

Built for reliable performance with proven technology from the makers of the number 1 monitor brand worldwide*.

- Get peace of mind with Premium Panel Guarantee¹.
- Reduce downtime with 3 years Advanced Exchange Service² during the Limited Hardware Warranty³ period.
- Minimize impact on the environment with a BFR/PVC-free monitor (excludes external cables), mercury-free LED panel, and more than 25% post-consumer recycled materials.
- Meet regulatory and environmental requirements such as EPEAT Gold⁵, TCO Certified Displays and ENERGY STAR[®].




For more information visit
www.dell.com/monitors

Thank you
for making
Dell monitors

#1
Worldwide*

Fully adjustable P2715Q offers multiple ways to adjust to your preferred viewing position:



Connectivity



- | | |
|------------------------------|-----------------------------|
| A AC power connector | F Audio line-out |
| B HDMI (MHL) | G USB upstream |
| C DisplayPort in | H USB downstream (4) |
| D Mini DisplayPort in | I Stand lock |
| E DisplayPort out | |



What's in the box?

Monitor, stand, cable cover, power cable (varies by country), DisplayPort cable (mini-DP to DP), USB 3.0 upstream cable (enables the USB ports on the monitor), drivers and documentation media, quick set up guide, Safety and Regulatory Information, Factory Color Calibration Report.

Dell 27 Monitor | P2715Q

Display	
Model number	P2715Q
Viewable image size (diagonal)	68.47 cm (27 inches)
Active display area	
Horizontal	596.74 mm (23.49 inches)
Vertical	335.66 mm (13.21 inches)
Maximum resolution	3840 x 2160 at 60Hz
Aspect ratio	16:9
Pixel pitch	0.1554 mm x 0.1554 mm
Brightness (typical)	50 to 350 cd/m ²
Color gamut (typical)	99% sRGB (delta E <3) 103.961% ⁴ (CIE1976)
Color depth	1.07 billion colors
Contrast ratio (typical)	1,000:1
Dynamic contrast ratio	2 million:1
Viewing angle (typical) (vertical/horizontal)	178°/178°
Response time (typical)	Fast mode: 6 ms gray-to-gray (typical) Normal mode: 8 ms gray-to-gray (typical)
Panel technology, surface	In-plane switching, anti-glare
Backlight	LED
Speakers (optional)	Dell Speaker Bar AC511
Bezel color	Black

Connectivity

Connectors	1 x mini-DisplayPort ⁶ , 1 x DisplayPort (in), 1 x DisplayPort (out), 1 x HDMI (MHL), 4 x USB 3.0 ⁷ , 1 x Audio Line out
------------	--

Design features

Stand	Height-adjustable stand (115 mm), tilt (5° forward or 21° backward typical), pivot, swivel and built-in cable management
Security	Security lock slot (security lock not included)
VESA mounting support (wall mount sold separately)	100 mm x 100 mm

Power

AC input voltage/frequency/current (typical)	100 to 240 VAC / 50 or 60 Hz ± 3 Hz / 1.8 A (maximum)
Power consumption (normal operation, typical)	50 W
Power consumption (active-off mode)	<0.5 W

Dimensions (with stand)

Height (compressed ~ extended)	423.86 mm (16.69 inches) ~ 538.86 mm (21.22 inches)
Width	640.74 mm (25.23 inches)
Depth	203.86 mm (8.03 inches)

Weight

Weight (panel only – no stand)	5.03 kg (11.10 lb)
Weight (with stand)	7.53 kg (16.60 lb)
Shipping weight	10.66 kg (23.50 lb)

Standard service plan

3 Years Advanced Exchange Service² & 3 Years Limited Hardware Warranty³

Environmental compliance

ENERGY STAR[®], EPEAT[®] Gold⁵, TCO Certified Displays, China Energy Label, RoHS, WEEE, ErP (EuP) Standards, Korea E-Standby

* Dell monitors are #1 Worldwide in 2013. Dell monitors are #1 in North America for the last 14 years (2000 to 2013). Source: NPD DisplaySearch Quarterly Desktop Monitor Shipment and Forecast Report. (Ad#G14000221)

** Registered in US and Canada only.

¹ In the event you discover even one bright pixel during the Limited Hardware Warranty period, a free panel exchange is guaranteed. (see pixel panel info located on Dell.com web page for complete details): <http://support.dell.com/support/topics/global.aspx/support/kcs/document?docid=414288>

² Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

³ For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see dell.com/warranty.

⁴ Color gamut (typical) is based on CIE1976 (103.961%) and CIE1931 (77.6%) test standards.

⁵ EPEAT Gold registered in the U.S. EPEAT registration varies by country. See www.epeat.net for registration status by country.

⁶ DisplayPort 1.2 – Supports High Bit Rate 2 (HBR2) and Multi-stream transport (MST). P2715Q does not support fast AUX transaction, 3D stereo transport and HBR (High bit rate) audio

⁷ One USB downstream port is for charging BC1.2 devices and also supports up to 2A when powering standard USB devices.

Product availability varies by country. Please contact your Dell representative for more information. Based on Dell document Ad#A14000531 dell.com/monitors

