

ASSEMBLED

Orator Floor Lectern MODEL #800X

FEATURES

- **Elegant upscale sound lectern for medium-sized venues like conference rooms, meeting halls and auditoriums**
- Two Microphones: one Handheld (9' cable) and one Tie-Clip/Lavalier (10' cable)
- Flexible gooseneck arm and digital time piece
- Upgraded Shock Mount holder to prevent feedback
- Input/Output lines for Media players, extension speakers, recording and playing MP3s
- Spacious reading surface illuminated by an attractive brass lamp
- Convenient storage on a 12"x4" shelf
- Four concealed easy-roll casters for easy mobility
- High pressure thermal-fused laminate on a MDF core
- Durable scratch resistance surface
- Minor Assembly Required, UPS

ILLUMINATED BY A BRASS LAMP

SHOWN IN MEDIUM OAK


THE ONLY UNPRECEDENTED WARRANTY ON ALL PRODUCTS
5 YEARS

sound


wireless sound



CLICK HERE TO VIEW MARKETING VIDEO



COLOR OPTIONS



4 CONCEALED EASY ROLL CASTERS

AVAILABLE ACCESSORIES



800X

TECHNICAL SPECIFICATIONS

DIMENSIONS	46"H x 22"W x 17"D
WEIGHT	63 lbs.
INSIDE SHELF	12"W x 4"D
POWER OUTPUT	40 Watts
MICROPHONES	2 Condenser type: Handheld with 9' Cable, Tie-Clip/Lavalier with 10' Cable
SPEAKERS	Four 6" Full Range
INPUTS	Two Mics, One Aux
WIRELESS	Switchable, Two Frequency
OUTPUTS	Line out 1: Extension Speaker, Line out 2: Media Recorder
CONTROLS	Four Volume, Bass/Treble, On/Off
FUSE	Internally Mounted, 2A
POWER SUPPLY	117V AC; 12V DC with Optional battery
RECHARGER	Internally mounted, with LED indicator



800.261.4112 | www.oklahomasound.com