

EZ930

720p Analog HD True Day/Night
Outdoor IR Bullet Camera


eZ.HD



Features

- 720P with high flexibility and performance for astounding image
- 1/2.8" Sony 1.37M pixels COMS, delivers amazing high sensitivity
- Varifocal 2.8~12mm DC iris lens to capture the desired field of view
- 80 IR LEDs for 35m/115ft. range (depending on scene IR reflectivity)
- D-WDR to improve the visibility under high contrast scene
- Provides 3D-Noise Reduction ensures less blurry moving subjects, vivid and high SN ratio images even under low light environments
- Support 720p & 960H Analog signal output, which can be easily switched by OSD
- The flexible angle viewing with its 3 Axis rotation design allows wall or ceiling mounting
- Internal wire system with anti-cut bracket
- Weather Resistant IP66 and built-in heater
- Supports Ceiling Mount and Wall mount

Dimensions



NEW



Specifications

Part number	EZ930
Pickup Device	1/2.8" Sony 1.37M pixels COMS
Video Format	NTSC/PAL (can be switched via OSD)
Effective Pixels	1280 (H) x 720 (V)
Scanning System	Progressive Scan
Sensitivity	0 Lux With IR On
S/N Ratio	Over 48dB (AGC off)
Electronic Shutter	Auto/Manual (x30~1/50,000) / Flk
Video Output	BNC 1.0Vp-p 75Ω
Gamma Correction	0.45
Lens Type	2.8mm-12mm DC Iris with ICR
BLC	OFF/BLC/HS BLC Selectable
AGC	0~15 Levels
White Balance	ATW/AWC-SET/Indoor/Outdoor/Manual/AWB
Sync Mode	Internal
Day/Night	Ext, Auto, Color, B/W
IR LED	80 Units
IR Distance	Up to 35m/115ft.(depending on scene IR reflectivity)
OSD Languages	12-Languages
DNR	2DNR/3DNR, OFF
DEFOG	Off/Auto(Under B/W Mode)
D-WDR	On/Off
Sens-UP	On/Off(x30~x2)
Mirror	Off/Mirror/V-Flip/Rotate
Motion Detection	Off/On for 4 selectable zones
Privacy Mask	Off/On for 4 selectable zones
Environmental	IP66 Weather Resistant
Power Source	12VDC/24VAC
Power Consumption	12VDC:12W / 24VAC:13.5W
Operating Temperature	-40°C~50°C / -40°F~122°F
Humidity	Less than 80%
Dimensions (L x W x H)	236 x 84 x 110mm / 9.29" x3.3" x4.3"
Weight	1100g / 2.42lbs
Certifications	CE, FCC, RoHS

* All product specifications are subject to change without notice
 * Models vary in different countries. Please visit EverFocus regional websites for detailed ordering information
 * Lens models and availability vary in different regions