

# 28" Ultra HD Monitor with MultiPicture Technology

3840x2160 Resolution for the Ultimate in Image Detail

**VG2860mhl-4K**



If you're writing thousands of lines of code, making financial forecasts, or viewing video surveillance footage, the efficiency of your work often comes down to the details on your monitor. That's why we created the ViewSonic® VG2860mhl-4K monitor. With stunning 3840x2160 resolution at a high refresh rate of 60Hz\*, this 28" monitor is engineered to deliver the ultimate in detail and clarity so that the finer points never go by unnoticed. When multiple projects need your attention, ViewSonic's exclusive MultiPicture functionality lets you view up to four Full HD video sources at once, while a fully adjustable ergonomic stand keeps you comfortable. The ViewSonic VG2860mhl-4K monitor delivers the screen size, incredible detail, and multitasking features you need to get your job done.

## **Key Features:**

Ultra HD 3840x2160 @ 60Hz\* native resolution

MultiPicture support for viewing up to 4 Full HD video sources

Future-proof DisplayPort (Full size and mini), HDMI, MHL and DVI inputs

Ergonomic tilt, swivel, pivot, and height-adjust

Exclusive ViewMode™ technology delivers superior color rendering and intuitive settings

## **Designed for:**


Business

Finance

Surveillance

# 28" Ultra HD Monitor with MultiPicture Technology

**VG2860mhl-4K**



## Specifications

<b>LCD PANEL</b>	Type	Color a-Si Active Matrix TFT LCD
	Display Area	24.4" horizontal x 13.4" vertical; 28.0" diagonal
	Optimum Resolution	3840x2160
	Brightness	300 cd/m <sup>2</sup> (typ.)
	Contrast Ratio	1,000:1 (typ.)
	Viewing Angles	170° horizontal, 160° vertical
	Colors	1.07B (true 8-bits + 2-bits FRC)
	Response Time	2ms (GTG)
	Backlight	White-light LED
	Backlight Life	30,000 hours (min.)
	Panel Surface	Anti-glare, hard-coating (3H)
<b>VIDEO INPUT</b>	Digital	DVI, HDMI / MHL, DisplayPort
	Frequency	Fh: 24~160kHz, Fv: 24~75Hz
	Sync	Separate Sync, Composite Sync, Sync on Green
<b>AUDIO OUTPUT</b>	Speakers	3-watt (x2)
<b>COMPATIBILITY</b>	PC	Up to 3840x2160
	Mac®	Up to 3840x2160
<b>CONNECTOR</b>	Video In	HDMI, HDMI / MHL, DisplayPort (x2), DVI-D
	Audio In	3.5mm mini jack
	Headphone	3.5mm mini jack
	USB Hub	USB 2.0 (x2), USB 3.0 (x2) USB Upstream
	Power	Internal power board
<b>CONTROLS</b>	Front Panel Buttons	Power, 1, Up, Down, 2
	OSD	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall (See user guide for complete OSD functionality)

<b>ERGONOMICS</b>	Tilt	Forward 5° / Back 37°
	Swivel	350°
	Height Adjust	0 ~ 150mm
	Pivot	90°
<b>POWER</b>	Voltage	AC 100~240V (universal), 50 / 60Hz
	Consumption	48W (typ.) / 56W (max.)
	Optimize	34W (typ.)
	Conserve	28W (typ.)
<b>OPERATING CONDITIONS</b>	Temperature	32~104° F (0~40° C)
	Humidity	10~90% (non-condensing)
<b>DIMENSIONS (W x H x D)</b>	Physical with Stand	26.0 x 19.0 x 10.5 in. / 659.7 x 483.4 x 266 mm
	Physical without Stand	26.0 x 15.4 x 1.9 in. / 659.7 x 391.0 x 49.3 mm
	Packaging	29.2 x 19.4 x 7.7 in. / 742 x 493 x 196 mm
<b>WEIGHT</b>	Net with Stand	17.2 lb. / 7.8 kg
	Net without Stand	11.7 lb. / 5.3 kg
	Gross	22.5 lb. / 10.2 kg
<b>WALL MOUNT</b>	VESA	100 x 100mm
<b>REGULATIONS</b>		CE, CB, RoHS, ErP, REACH, WEEE, TCO, WHQL, cULus, FCC-B, ENERGY STAR 6.0, EPEAT Gold, Mexico Energy
<b>RECYCLE/DISPOSAL</b>		Please dispose of in accordance with local, state, or federal laws
<b>WARRANTY</b>		Three-year limited warranty on parts, labor and backlight

## Optional Accessories

HDMI to DVI cable 6FT .....	CB-00008948
DVI-D to DVI-D Cable 6FT .....	CB-00008187
Mini DisplayPort to DisplayPort Cable 6FT .....	CB-00010958
DisplayPort to DisplayPort Cable 30FT .....	CB-00010684
DisplayPort to DisplayPort Cable 6FT .....	CB-00010555
DisplayPort to DVI Adapter .....	LCD-CABLE-001

## What's in the box?

VG2860mhl-4K monitor, Power cable, DisplayPort cable, MHL cable, Audio cable, USB 3.0 cable, Quick Start Guide, ViewSonic Wizard CD (with user guide)



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by TUV NORD.