

Cat5e patch cable with snagless RJ45 connectors – 3m, orange

StarTech ID: 45PAT3MOR



The 45PAT3MOR Cat5e patch cable (3m) meets or exceeds all Cat 5e cable specifications to ensure reliable Ethernet network connections, and features a durable orange PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles, reducing the risk of cable failure.

Constructed of only top quality materials, this Cat5e patch cord delivers reliable performance and is backed by our lifetime warranty.

100% copper for outstanding value

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

24-gauge wire for high-performance network connection

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

50-micron gold connectors provide peak conductivity

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Applications

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Features

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

Technical Specifications

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Type	PVC - Polyvinyl Chloride
Fire Rating	CM Rated
Cable Type	Snag-less
Connector A	1 - RJ-45 Male
Connector B	1 - RJ-45 Male
Cable Rating	CAT5e - 350 MHz
Color	Orange
Wire Gauge	24 AWG
Cable Length	3 m [9.8 ft]
Product Length	3 m [9.8 ft]
Product Weight	110 g [3.9 oz]
Shipping (Package) Weight	130 g [4.6 oz]
Package Quantity	1
Included in Package	1 - 3m Orange Snagless Cat5e UTP Patch Cable

Certifications, Reports and Compatibility



RoHS Compliant
Available