

Voyager 1452g

Upgradeable Area-Imaging Wireless Scanner

Across many industries, 2D barcoding is the standard. Not only is it possible to hold much more data in a 2D code, but government regulations and supplier mandates are requiring their adoption. Enterprises are also looking to leverage emerging trends that require area-imaging technology – today or in the near future – without the need to purchase additional scanning hardware, or settle for reduced scanning performance.

The Voyager™ 1452g scanner allows enterprises to embrace area-imaging at their own pace, and in the most cost-effective manner. Built on the durable platform of Honeywell's world-renowned Voyager series handheld scanners, the Voyager 1452g scanner delivers omnidirectional reading of linear barcodes, plus the ability to affordably upgrade the device to enable 2D barcode scanning – either at the time of purchase, or as data capture needs evolve.

Incorporating a Bluetooth® Class 2 radio, the Voyager 1452g scanner has a wireless range of up to 10 meters (33 feet) from the base, enabling maximum operator freedom while eliminating the hassle and trip-hazard of a tethered cable. For added convenience, an included paging system helps locate misplaced scanners with visual and auditory signals.

The Voyager 1452g scanner offers an exceptional value for enterprises that require the versatility of area-imaging technology today or may need it in the future. Produced by a company with decades of experience in engineering-quality data capture solutions, the Honeywell Voyager 1450g wireless area-imaging scanner is a durable and scalable investment.



The Voyager 1452g scanner provides wireless omnidirectional reading of linear barcodes, with the ability to affordably upgrade to PDF and 2D barcode scanning at your convenience.

FEATURES & BENEFITS



Bluetooth wireless technology facilitates the scanning of all standard 1D, PDF, and 2D barcodes up to 10 meters (33 feet) from the base (depending on the environment).



Unlike traditional laser scanners, the 1D version of the Voyager 1452g scanner can read barcodes omnidirectionally, making it ideal for presentation scanning.



For those who only require 1D scanning now but anticipate 2D scanning in the future, the Voyager 1452g scanner can be affordably upgraded from 1D to 2D scanning at any time.



Scans coupons, mobile tickets, and digital wallets from the screens of mobile devices.



The field-replaceable lithium-ion battery provides 14 hours or more of use, depending on scanning volume.

Voyager 1452g Technical Specifications

WIRELESS

Radio/Range: 2.4 GHz to 2.5 GHz (ISM Band)
Adaptive Frequency Hopping Bluetooth v2.1 Class 2: 10 m (33 ft) line of sight

Data Rate (Transmission Rate): Up to 1 Mbps

Battery: 2,400 mAh lithium-ion battery

Number of Scans: Up to 40,000 scans per charge

Expected Hours of Operation: 14 hours

Expected Charge Time: 4.5 hours

MECHANICAL/ELECTRICAL

Dimensions (L x W x H):

Scanner (1452g): 62 mm x 173 mm x 82 mm
(2.5 in x 6.8 in x 3.2 in)

Charger/Communication Base (CCB01-010BT-V7N): 132 mm x 102 mm x 81mm
(5.2 in x 4.0 in x 3.2 in)

Weight:

Scanner: 210 g (7.4 oz)

Charger/Communication Base: 179 g (6.3 oz)

Operating Power (Charging):

Scanner: N/A

Charger/Communication Base: 5 W (1A @ 5V)

Non-Charging Power:

Scanner: N/A

Charger/Communication Base: 0.5 W (0.1A @ 5V)

Host System Interfaces:

Scanner: N/A

Charger/Communication Base: USB, Keyboard Wedge, RS-232 TTL, IBM 46xx (RS485)

ENVIRONMENTAL

Operating Temperature:

Scanner:

Charging: 5°C to 40°C (41°F to 104°F)

Non-Charging: 0°C to 50°C (23°F to 122°F)

Charger/Communication Base:

Charging: 5°C to 40°C (41°F to 104°F)

Non-Charging: 0°C to 50°C (32°F to 122°F)

Storage Temperature with Battery:

Scanner:

For storage up to 90 days: -20°C to 35°C
(-4°F to 95°F)

For storage up to 1 year: -20°C to 20°C
(-4°F to 68°F)

Charger/Communication Base: -40°C to 70°C
(-40°F to 158°F)

Humidity:

Scanner: 0 to 95% relative humidity, non-condensing

Charger/Communication Base: 0 to 95% relative humidity, non-condensing

Drop:

Scanner: Designed to withstand 30 1.5 m (5 ft) drops to concrete

Charger/Communication Base: Designed to withstand 50 1.0 m (3.3 ft) drops to concrete

Tumble:

Scanner: Designed to withstand 1,000 tumbles from 0.5 m (1.64 ft)

Environmental Sealing:

Scanner: IP42

Charger/Communication Base: IP41

Light Levels:

Scanner: 0 to 100,000 lux
(9,290 foot-candles)

Charger/Communication Base: N/A

SCAN PERFORMANCE

Scan Pattern: Area Image (640 x 480 pixel array)

Motion Tolerance: Up to 10 cm/s (4 in/s) for 13 mil UPC at optimal focus

Scan Angle: Horizontal 37.8°; Vertical 28.9°

Symbol Contrast: 35% minimum reflectance difference

Pitch, Skew: ±60°, ±70°

Decode Capability:

1452g1D: All standard 1D symbologies

1452g2D: All standard 1D, PDF417, and 2D symbologies

Warranty: 3-year factory warranty

TYPICAL PERFORMANCE*	EXTENDED RANGE (ER)
NARROW WIDTH	
5 mil Code 39	45 mm – 107 mm (1.8 in – 4.2 in)
13 mil UPC	37 mm – 260 mm (1.4 in – 10.2 in)
20 mil Code 39	42 mm – 360 mm (1.6 in – 14.2 in)
6.7 mil PDF417	42 mm – 107 mm (1.6 in – 4.2 in)
10 mil DM**	42 mm – 107 mm (1.6 in – 4.2 in)
20 mil QR	32 mm – 210 mm (1.2 in – 8.3 in)

* Performance may be impacted by barcode quality and environmental conditions.

** Data Matrix (DM).

For a complete listing of all compliance approvals and certifications, please visit www.honeywellaidc.com/compliance.

For a complete listing of all supported barcode symbologies, please visit www.honeywellaidc.com/symbologies.

Voyager is a trademark or registered trademark of Honeywell International Inc. in the United States and/or other countries.

Bluetooth is a trademark or registered trademark of Bluetooth SG, Inc. in the United States and/or other countries.

Specifications are subject to change without notice.

For more information

www.honeywellaidc.com

Honeywell Safety and Productivity Solutions

9680 Old Bailes Road

Fort Mill, SC 29707

800-582-4263

www.honeywell.com

Voyager 1452g Data Sheet | Rev B | 10/17
© 2017 Honeywell International Inc.

Honeywell