



IK-TR-911

FULL TRAVEL KEYBOARD WITH ATTACHMENT VERSATILITY

Designed to fit into existing mobile mounting systems, iKey's new Transformer Keyboard has built-in high-speed USB hubs and modular options to accommodate multiple custom configurations, making this the ideal all-in-one, on-the-go solution. These rugged keyboards are built for use in EMS, police and service vehicles. The Transformer Keyboard is also fully sealed and is resistant to dirt, dust and spills that can ruin most keyboards. Features 12 Function Keys 88-Key Functionality Integrated Backlighting Integrated Touchpad Mobile Mounting Holes One-Touch Emergency Key

Product Code IK-TR-911

SHOCK	3x11 ms pulses of 50g on each of 3 axes
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2kHz DURATION OF TEST PER AXIS: 3 hours
POWER	USB: 35mA@5V (from CPU port)
TEMPERATURE RANGE	STORAGE: -40C to 75C (-40F to 167F) OPERATING: -20C to 60C (-4F to 140F)
WEIGHT	2.0 lbs +/- 0.10 lbs (0.90 kg +/- 0.05 kg)
WARRANTY	1 Year Limited Warranty
HUMIDITY	100% Humidity Resistant
DIMENSIONS	302.77 x 194.3 x 31.24 mm (11.92 x 7.65 x 1.23 inches)
MODEL NUMBERS	IK-TR-911