


Full HD 1080p 2MP Indoor/Outdoor Flush Mount Dome IP Camera with Integrated Junction Box

O2D7M 3.3-10mm auto iris varifocal motorized lens, dark grey housing

Features

- Supports up to Full HD 1080p @ 30fps
- Motorized lens with auto focus
- Built-in standard PoE (IEEE 802.3af)
- Flush mount design
- Included junction box integrates with enclosure for wall/ceiling mounting
- Smart IR function provides vivid image with no saturation in darkness
- True Day/Night operation (IR cut filter)
- IR Range: 65' (depending on scene reflection)
- Supports H.264 and MJPEG codecs
- 2-way audio communication
- Micro SD card slot (card not included)
- Sensor input and relay output
- Built-in heater reduces condensation under any weather condition
- IP66 compliant
- Conformant with ONVIF profile S*
- 2 year warranty



Camera Specifications

Image Sensor.....	Progressive scan 1/2.8" CMOS, 2MP
Maximum Resolution	1920x1080
Minimum Illumination	0 lux (IR LED on)
IR Range	65' (depending on scene reflection)
White Balance	Automatic, Manual
Exposure Control	Yes
Digital Slow Shutter.....	Yes
Backlight.....	BLC/HSBLC
Day/Night	IR cut filter
DNR.....	Yes

Video Specifications

Supported Resolutions....	1920x1080/1280x720/704x480/352x240 @ 30fps
Compression	H.264, MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

Audio Specifications

Mono Input	64Kbps G.711
Mono Output	64Kbps G.711

External Terminal Specifications

Ethernet.....	10/100 Mbps
Alarm	1 sensor input, 1 output
Video	BNC out
Audio	1 input, 1 output
Power	DC jack
Storage.....	Micro SD slot

Network Specifications

Protocols	IPv4, TCP, UDP, RTCP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, Bonjour
DDNS support.....	Speco DDNS (free of charge)

Network Specifications (continued)

Security	User ID & Password protection, IP address filtering, HTTPS
User Access	10 simultaneous users Performance may vary depending on resolution and number of connections

System Specifications

PoE.....	Standard (IEEE 802.3af)
Analytics	Motion detection (3 regions), tampering alarm, trip zone
Alarm Triggers.....	Motion, sensor input, tamper detection, trip zone
Alarm Events.....	FTP video/image file upload, email image upload, micro SD card recording, relay out
Video Buffer.....	Configurable pre-record & post-record
Image Settings	Privacy mask

Client Specifications

Web Browser Support....	Windows (Internet Explorer 8 and up)
PC Application.....	SecureGuard®

Operating & Unit Specifications

Power Supply	PoE, 12VDC (power supply not included)
Power Consumption.....	8W
Operating Temperature ...	-4° F – 122° F
Operating Humidity	8% – 80% RH
Unit Dimensions.....	4.7" (H) x 5.9" (Dia.)
Unit Weight.....	2.2 lbs.
Certifications	FCC, RoHS
Included in Package.....	Unit, CD (manual, software), mounting screws, L wrench

*Visit www.specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/22/16

Optional Accessories

