

Computer power cord - C19 to C20, 14 AWG, 10 ft

StarTech ID: *PXTC19201410*



This C19 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high-power connections, making it perfect for server applications and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 10 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Designed and constructed of high-quality materials, the PXTC19201410 power cord is backed by our lifetime warranty.

Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 10 feet

Features

- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS compliant

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SJT
Number of Conductors	3
Connector A	1 - IEC 60320 C19 Power
Connector B	1 - IEC 60320 C20 Power
Cable Length	10 ft [3 m]
Color	Black
Product Length	10 ft [3 m]
Product Weight	1.9 oz [54 g]
Wire Gauge	14 AWG
Input Current	15 A
Input Voltage	250 AC
Package Quantity	1
Shipping (Package) Weight	1.9 oz [54 g]
Included in Package	1 - 10 ft 14 AWG Computer Power Cord - C19 to C20

Certifications, Reports and Compatibility

