

IDEA Panoramic

The latest IDEA™ Panoramic features upgraded durability, surface uniformity and rigidity to ensure a superior interactive experience. The erasable surface is designed to cover the wall of a classroom, is hotspot-free under projection, and now comes with new standard features - all IDEA Screens are magnetic and have a thin frame. It can be used with an ultra short throw projector as an interactive screen or as a whiteboard with dry-erase markers. A tray for markers make the IDEA Panoramic a great upgrade to any classroom. New sizes available.

Features

- Three panel design to cover large walls
- Projection-quality surface can be written on with dry-erase markers
- Extruded aluminum frame in black or silver finish
- 24" tray for storing markers, erasers and interactive tools (full size tray available)
- Wall brackets for easy installation
- Offers a gain of 2.5, along with a 25-degree viewing angle
- GREENGUARD® Certified and GREENGUARD® Gold Certified
- Indoor Air Quality Certified

Optional Accessories:

- Whiteboard Mount
- IDEA Replacement Marker Kit
- Green Laser Pointers
- Red Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer




16:9 HDTV Format

Viewing Area (H x W)		Center Panel Viewing Area (H x W)		Center Panel Nominal Diagonal		Overall Dimensions	
in.	cm	in.	cm	in.	cm	in.	cm
36" x 144"	91 x 366	36" x 64"	91 x 163	73"	185	36¾" x 144¾"	93 x 368
36" x 168"	91 x 427	36" x 64"	91 x 163	73"	185	36¾" x 168¾"	93 x 429
36" x 192"	91 x 488	36" x 64"	91 x 163	73"	185	36¾" x 192¾"	93 x 490
46" x 144"	117 x 366	46" x 81¼"	117 x 208	94"	239	46¾" x 144¾"	119 x 368
46" x 168"	117 x 427	46" x 81¼"	117 x 208	94"	239	46¾" x 168¾"	119 x 429
46" x 192"	117 x 488	46" x 81¼"	117 x 208	94"	239	46¾" x 192¾"	119 x 490
50" x 144"	127 x 366	50" x 89"	127 x 226	102"	259	50¾" x 144¾"	129 x 368
50" x 168"	127 x 427	50" x 89"	127 x 226	102"	259	50¾" x 168¾"	129 x 429
50" x 192"	127 x 488	50" x 89"	127 x 226	102"	259	50¾" x 192¾"	129 x 490
53" x 144"	135 x 366	53" x 94¼"	135 x 239	108"	274	53¾" x 144¾"	137 x 368
53" x 168"	135 x 427	53" x 94¼"	135 x 239	108"	274	53¾" x 168¾"	137 x 429
53" x 192"	135 x 488	53" x 94¼"	135 x 239	108"	274	53¾" x 192¾"	137 x 490
59½" x 144"	151 x 366	59½" x 106"	151 x 269	121"	307	60¼" x 144¾"	153 x 368
59½" x 168"	151 x 427	59½" x 106"	151 x 269	121"	307	60¼" x 168¾"	153 x 429
59½" x 192"	151 x 488	59½" x 106"	151 x 269	121"	307	60¼" x 192¾"	153 x 490

16:10 Wide Format

Viewing Area (H x W)		Center Panel Viewing Area (H x W)		Center Panel Nominal Diagonal		Overall Dimensions	
in.	cm	in.	cm	in.	cm	in.	cm
36" x 144"	91 x 366	36" x 57½"	91 x 146	68"	173	36¾" x 144¾"	93 x 368
36" x 168"	91 x 427	36" x 57½"	91 x 146	68"	173	36¾" x 168¾"	93 x 429
36" x 192"	91 x 488	36" x 57½"	91 x 146	68"	173	36¾" x 192¾"	93 x 490
46" x 144"	117 x 366	46" x 73½"	117 x 187	87"	221	46¾" x 144¾"	119 x 368
46" x 168"	117 x 427	46" x 73½"	117 x 187	87"	221	46¾" x 168¾"	119 x 429
46" x 192"	117 x 488	46" x 73½"	117 x 187	87"	221	46¾" x 192¾"	119 x 490
50" x 144"	127 x 366	50" x 80"	127 x 203	94"	239	50¾" x 144¾"	129 x 368
50" x 168"	127 x 427	50" x 80"	127 x 203	94"	239	50¾" x 168¾"	129 x 429
50" x 192"	127 x 488	50" x 80"	127 x 203	94"	239	50¾" x 192¾"	129 x 490
53" x 144"	135 x 366	53" x 84¼"	135 x 215	100"	254	53¾" x 144¾"	137 x 368
53" x 168"	135 x 427	53" x 84¼"	135 x 215	100"	254	53¾" x 168¾"	137 x 429
53" x 192"	135 x 488	53" x 84¼"	135 x 215	100"	254	53¾" x 192¾"	137 x 490
59½" x 144"	151 x 366	59½" x 95¼"	151 x 242	112"	284	60 ¼" x 144¾"	153 x 368
59½" x 168"	151 x 427	59½" x 95¼"	151 x 242	112"	284	60 ¼" x 168¾"	153 x 429
59½" x 192"	151 x 488	59½" x 95¼"	151 x 242	112"	284	60 ¼" x 192¾"	153 x 490

*Add ¾" (2 Cm.) to overall frame height for marker tray and right angle brackets.



IDEA

Half Angle: 25° Gain: 2.5

Product images



Frame



A Milestone AV Technologies Brand

3100 North Detroit Street
Warsaw, Indiana 46582
P: 574.267.8101 or 800.622.3737
F: 574.267.7804 or 877.325.4832
E: info@da-lite.com
www.da-lite.com

DL-0491 08.14

© 2014 Milestone AV Technologies LLC. Printed in U.S.A.