

# Tensioned Large Cosmopolitan Electro

For larger venue installs, the Tensioned Large Cosmopolitan® Electro® is a ceiling or wall mounted electric screen. A variety of finishes and veneer options are available.

## Features

- In-the-roller motor mounting system
- Tensioning Cable System to prevent warping and ensure even lateral tension
- Decora-style, three-position wall switch
- Standard black backing retains projected brightness on front projection surfaces
- Seamless surfaces
- Two-piece aluminum case with mounting brackets for wall or ceiling mount installation
- Available with built-in low voltage control, or Video Projector Interface (screen trigger) or silent motor
- Standard black powder-coated aluminum finish; available in white or veneer upon request
- Smooth Roll Technology to keep your screen perfectly flat
- Slim-Tab, a lower profile, stronger tab design to keep your screen perfectly taut

## Optional Accessories:

- Single Motor Low Voltage Control System
- Radio Frequency Wireless Remote Single Motor LVC
- Infrared Wireless Remote Single Motor LVC
- SCB-100
- Video Projector Interface
- Key Operated, 110 Volt Switch
- Locking Switch Cover Plate
- Dual Motor Low Voltage Control System
- Radio Frequency Wireless Remote - Dual Motor LVC
- Infrared Wireless Remote Dual Motor LVC
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



## 16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
92" x 164"	234 x 417	188"	478	186"	472
108" x 192"	274 x 488	220"	559	215½"	547

## 16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
100" x 160"	254 x 406	189"	480	182½"	464
110" x 176"	279 x 447	208"	528	199¾"	507
120" x 192"	305 x 488	226"	574	217"	551

## 4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
108" x 144"	274 x 366	180"	457	167½"	425
120" x 160"	305 x 406	200"	508	185"	470
126" x 168"	320 x 427	210"	533	194"	493
132" x 176"	335 x 447	220"	559	203"	516
144" x 192"	366 x 488	240"	610	220½"	560

Available with the Following Screen Surfaces



**HD Progressive 0.9**  
Half Angle: 85° Gain: 0.9




**HD Progressive 1.1**  
Half Angle: 85° Gain: 1.1



**HD Progressive 1.3**  
Half Angle: 75° Gain: 1.3



**Da-Mat**  
Half Angle: 60° Gain: 1.0



**High Contrast Da-Mat**  
Half Angle: 45° Gain: 0.8



**Cinema Vision**  
Half Angle: 45° Gain: 1.3



**High Contrast Cinema Vision**  
Half Angle: 50° Gain: 1.1



**Pearlescent**  
Half Angle: 40° Gain: 1.5



**Dual Vision**  
Half Angle: 65° Gain: 0.9



**Da-Tex**  
Half Angle: 30° Gain: 1.3


Product images



Black Case (Standard)



White Case



Dark Veneer Case



Light Veneer Case



A Milestone AV Technologies Brand

3100 North Detroit Street  
Warsaw, Indiana 46582  
P: 574.267.8101 or 800.622.3737  
F: 574.267.7804 or 877.325.4832  
E: info@da-lite.com  
www.da-lite.com

DL-0443 0714

© 2014 Milestone AV Technologies LLC. Printed in U.S.A.