

## Computer power cord - C19 to C20, 14 AWG, 6 ft

StarTech ID: PXTc19C20146



This C19-to-C20 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for server applications and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 6 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXTc19C20146 power cord is backed by a lifetime warranty.

### Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 6 feet

### Features

- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS compliant

## Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SJT
Number of Conductors	3
Connector A	1 - IEC 60320 C19 Power
Connector B	1 - IEC 60320 C20 Power
Cable Length	6 ft [1.8 m]
Color	Black
Product Length	6 ft [1.8 m]
Product Weight	1.9 oz [54 g]
Wire Gauge	14 AWG
Input Current	15 A
Input Voltage	250 AC
Package Quantity	1
Shipping (Package) Weight	1.9 oz [54 g]
Included in Package	1 - 6 ft 14 AWG Computer Power Cord - C19 to C20

## Certifications, Reports and Compatibility

