

Computer power cord - NEMA 5-15P to C19, 14 AWG, 3 ft

StarTech ID: PXT515C19143



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 3 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515C19143 power cord is backed by a lifetime warranty.

Applications

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 3 feet

Features

- Rated to carry 125V at 15A
- 14 AWG wire
- UL, RoHS compliant

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SJT
Number of Conductors	3
Connector A	1 - NEMA 5-15 Power (North America) Plug
Connector B	1 - IEC 60320 C19 Power
Cable Length	3 ft [0.9 m]
Color	Black
Product Length	3 ft [0.9 m]
Product Weight	0.8 oz [24 g]
Wire Gauge	14 AWG
Input Current	15 A
Input Voltage	125 AC
Package Quantity	1
Shipping (Package) Weight	7.2 oz [204 g]
Included in Package	1 - 3 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19

Certifications, Reports and Compatibility

