

Lexmark MX710 and MX711 Series

Monochrome Laser Multifunction Product

More versatility. More solutions. More capacity.

There's no such thing as too much of a good thing. The Lexmark MX710 Series multifunction product (MFP) delivers faster print, copy and scan speeds—plus productivity solutions too. For even more advanced solutions, go with the MX710dhe, or the MX711dhe with hard disk drive.



MX711dhe/dhe

Get more done. Even faster.

Now you can achieve much more in less time. Smoother workflows and faster speeds are just some of the great features that will help your business be more productive.

Faster processing - Improve your print, scan and copy speeds by taking advantage of up to 3 GB of upgradable memory, an 800 MHz dual-core processor and Gigabit Ethernet.

Reliable performance - Easily print up to 25,000 pages per month, plus enjoy fewer maintenance hassles, thanks to our state-of-the-art paper handling.

Keep jobs moving - With a maximum input capacity of up to 3,300 sheets and a high yield toner cartridge, you won't have to add paper or change cartridges as often.

Get work done quickly - Enjoy print and copy speeds up to 63 pages per minute, produce your first page in as little as 4 seconds and scan a two-sided document in a single pass. Want to print or copy up to 70 pages per minute? Get the MX711.

Look professional. Work smart.

Using a multifunction printer is easier than you think. Our system's easy-to-read touch screen saves steps with the press of a button, so you can focus more on business.

Smart and easy to use - A vibrant 7-inch color touch screen on the MX710 provides access to pre-installed workflow solutions. Want a larger 10.2-inch touch screen? Get the MX711.

Front USB port - Print without a PC using our convenient USB port that lets you walk up, preview and print PDFs and many other file formats.

Print on a wide range of media - With built-in 2-sided printing and the ability to print on diverse materials, you can do more for your business and use less paper.

Innovative toner that optimizes performance - Get greater system performance with Lexmark's Unison™ Toner, which delivers consistent image quality from first print to last.

Intelligent workflow. Secure design.

Our preloaded business solutions simplify your work processes and increase productivity. Ultra-advanced security capabilities provide maximum protection for your critical business data.


Print anytime and anywhere⁶ - With this system, you can print from desktops as well as mobile devices that can run applications.

Apps make it easy - Pre-loaded solutions work much like mobile phone apps. Touch the screen and access shortcuts to scan, print, copy or send faxes, emails and other documents fast.

Enjoy enterprise-level security - Now you can authenticate, authorize and audit employee usage. You can also protect sensitive data using standard network security protocols, data encryption and disk wiping capabilities.

Identify potential risks - Track more than 100 variables and events, including user activity, with Audit Logging. It's designed to work with your intrusion detection system in real time.

Lexmark MX710 and MX711 Series Monochrome Laser Multifunction Printer



Product specifications

	Lexmark MX510de	Lexmark MX511de	Lexmark MX511dhe
Printing			
Function	Printing, Network Scanning, Faxing, Copying, Color Scanning		
Display	Lexmark e-Task 7-inch (17.8 cm) color touch screen	Lexmark e-Task 10.2-inch (25.9 cm) color touch screen	Lexmark e-Task 10.2-inch (25.9 cm) color touch screen
Print Speed: Up to ⁴	Black: 63 ppm	Black: 70 ppm	Black: 70 ppm
Time to First Page: As fast as	Black: 4.4 seconds	Black: 4.0 seconds	Black: 4.0 seconds
Print Resolution	Black: 600 x 600 dpi, 1200 Image Quality, 2400 Image Quality, 1200 x 1200 dpi		
Memory / Processor	Standard: 512 MB / Maximum: 2560 MB / Processor: Dual Core, 800 MHz	Standard: 1024 MB / Maximum: 3072 MB / Processor: Dual Core, 800 MHz	Standard: 1024 MB / Maximum: 3072 MB / Processor: Dual Core, 800 MHz
Hard Disk	Included in configuration	Option available	Included in configuration
Recommended Monthly Page Volume ²	5000 - 25000 pages		
Maximum Monthly Duty Cycle: Up to ³	275000 pages per month	300000 pages per month	300000 pages per month
Copying			
Copy Speed: Up to ⁴	Black: 63 cpm	Black: 70 cpm	Black: 70 cpm
Time to First Copy: As fast as	Black: 4.2 seconds	Black: 4.0 seconds	Black: 4.0 seconds
Color Scanning			
Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (Single Pass Duplex) / 150 pages 20 lb or 75 gsm bond		
Duplex Scan Speed: Up to	A4/Ltr, Black: 70 / 72 sides per minute - A4/Ltr, Color: 66 / 68 sides per minute		
Simplex Scan Speed: Up to	A4/Ltr, Black: 67 / 70 sides per minute - A4/Ltr, Color: 67 / 70 sides per minute		
Optical Scanning Resolution	600 X 600 ppi (black), 300 X 300 ppi (color)		
Faxing			
Modem Speed	ITU T.30, V.34 Half-Duplex, 33.6 Kbps		
Supplies⁵			
Laser Cartridge Yields	25,000 ¹ -page High Yield Cartridge, 6,000 ¹ -page Cartridge	45,000 ¹ -page Extra High Yield Cartridge, 25,000 ¹ -page High Yield Cartridge, 6,000 ¹ -page Cartridge	45,000 ¹ -page Extra High Yield Cartridge, 25,000 ¹ -page High Yield Cartridge, 6,000 ¹ -page Cartridge
Cartridge(s) Shipping with Product	10,000 ¹ -page Starter Return Program Toner Cartridge	25,000 ¹ -page High Yield Return Program Toner Cartridge	25,000 ¹ -page High Yield Return Program Toner Cartridge
Paper Handling			
Included Paper Handling	Integrated Duplex, 550-Sheet Output Bin, 100-Sheet Multipurpose Feeder, 550-Sheet Input	Integrated Duplex, 550-Sheet Input, 100-Sheet Multipurpose Feeder, 550-Sheet Output Bin	Integrated Duplex, 550-Sheet Input, 550-Sheet Output Bin, 100-Sheet Multipurpose Feeder
Optional Paper Handling	550-Sheet Lockable Tray, 2100-Sheet Tray, 250-Sheet Tray, 550-Sheet Tray, 250-Sheet Lockable Tray	550-Sheet Lockable Tray, 250-Sheet Lockable Tray, 2100-Sheet Tray, 250-Sheet Tray, 550-Sheet Tray	550-Sheet Lockable Tray, 250-Sheet Lockable Tray, 550-Sheet Tray, 250-Sheet Tray, 2100-Sheet Tray
Paper Input Capacity: Up to	Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 3300 pages 20 lb or 75 gsm bond		
Paper Output Capacity: Up to	Standard: 550 pages 20 lb or 75 gsm bond / Maximum: 550 pages 20 lb or 75 gsm bond		
Media Types Supported	Refer to the Card Stock & Label Guide, Paper Labels, Integrated Labels, Dual Web Labels, Card Stock, Envelopes, Transparencies, Plain Paper		
Media Sizes Supported	A6, Oficio, Universal, Statement, Folio, DL Envelope, B5 Envelope, A4, 7 3/4 Envelope, 10 Envelope, 9 Envelope, A5, C5 Envelope, Executive, JIS-B5, Legal, Letter		
General			
Standard Ports	Rear USB 2.0 Specification Hi-Speed Certified Port (Type A), One Internal Card Slot, Front USB 2.0 Specification Hi-Speed Certified Port (Type A), USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000)		
Optional Network Ports / Optional Local Ports	Internal MarkNet N8350 802.11b/g/n Wireless / Internal 1284-B Bidirectional Parallel, Internal RS-232C serial		
Noise Level, Operating	Printing: 57 dBA / Copy: 58 dBA / Scan: 57 dBA	Printing: 58 dBA / Copy: 58 dBA / Scan: 57 dBA	Printing: 58 dBA / Copy: 58 dBA / Scan: 57 dBA
Product Warranty	1-Year Onsite Service, Next Business Day		
Size (in. - H x W x D) / Weight (lb.)	28.6 x 21.6 x 22.8 in. / 95.4 lb.		

¹ Average standard page yield value declared in accordance with ISO/IEC 19752. ² "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ³ "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ⁴ Print and copy speeds measured in accordance with ISO/IEC 24734, excludes first set of test documents. For more information see: www.lexmark.com/ISOspeeds. ⁵ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁶ For more information on Lexmark Mobile Solutions see: http://www.lexmark.com/en_US/solutions/business-solutions/mobile-print/index.shtml



Unison is a trademark of Lexmark International, Inc. Information in this document is subject to change without notice. ENERGY STAR® is a U.S. registered mark. All other trademarks are the property of their respective owners. Lexmark and Lexmark with the diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc.