


HSM® Powerline

FA500.3 industrial shredder

Designed for destroying large amounts of media and for continuous operation.



- Material infeed via a conveyor belt for optimum loading and maximum throughputs
- Practical loading table for simple loading
- Touch sensitive keypad for continuous and reverse operations
- Auto stop with LED indicates when shred bin is full
- Automatic reverse for paper jams
- Installed external oiler included
- Convenient trolley for shred-bin bag
- Very sturdy gear motor with chain drive for maximum throughputs
- Transportable on wheels
- Anti-Jam technology designed to easily and quickly reverse out paper in the event the machine is overloaded
- Uses a 168 gallon capacity shred bag; Part #HSM2728



HSM part#	HSM1991	HSM1993
Cutting type	Cross cut	Cross cut
Cutting size	9/32" x 1 1/2" - 3 5/32"	1/16" x 9/16"
Security level DIN 32757-1	3	4
Security level DIN 66399	P-3 / O-2 / T-3 / E-2	P-5 / O-4 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	500 - 550	120 - 130
Cutting Speed	42 ft / min	42 ft / min
Throat opening	20"	20"
Motor at max. no. of sheets	9.2kW	9.2kW
Motor power (horsepower)	10	12.75
Voltage	3x208 V / 60Hz	3x208 V / 60Hz
Dimensions (H x W x D)	71" x 46" x 71"	71" x 46" x 71"
Weight	1,742 lbs	1,742 lbs
Shred-bin volume	140 gal	140 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service: 800.613.2110

Great Products, Great People.

HSM®