

C16 personal shredder

Compact shredder for personal or home office use



- Entry level personal/home office model designed for 1 to 3 users
- Also shreds credit and store cards
- Automatic start/stop via photo eye sensor
- Reverse button with multifunction
- Folding safety element with contact protection
- Cutting rollers are V-Tek technology by HSM with specially hardened steel rollers that save valuable energy
- Level indicator through inspection window
- Handle recess on the top to empty waste with ease
- Automatic stop when the shredded material is removed
- Quiet operating sound minimizes noise development in the workplace
- Energy Management Control System Zero Power: does not consume any power in standby mode
- Anti-Jam Technology designed to easily and quickly reverse out paper in the event the machine is overloaded
- Made in Germany
- 11 gallon waste bag capacity; Part #HSM1310



HSM part#	HSM1900	HSM1901	HSM1902
Cutting type	Strip cut	Strip cut	Cross cut
Cutting size	1/8"	1/4"	5/32" x 1"
Security level DIN 32757-1	2	2	3
Security level DIN 66399	P-2 / T-2 / E-2	P-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	13 - 15	16 - 18	6 - 7
Cutting speed	8.6 ft / min	8.6 ft / min	8.6 ft / min
Throat opening	8.8"	8.8"	8.8"
Motor at max. no. of sheets	300W	300W	300W
Motor power (horsepower)	0.40	0.40	0.40
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	17.9" x 14.4" x 11.3"	17.9" x 14.4" x 11.3"	17.9" x 14.4" x 11.3"
Weight	8.8 lbs	8.8 lbs	9.9 lbs
Shred-bin volume	6.6 gallons	6.6 gallons	6.6 gallons
Cutting capabilities			

All technical specifications are approximate values. Technical and design modifications reserved.