

## B24 office shredder

For use by the desk



- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Automatic switches to energy-saving mode in 2 minutes after last use; switches off entirely if not used for 1 hour; temporary mode for small shredding jobs; and permanent mode for large shredding jobs
- Multifunctional control key with reversing function
- Shred bin level indicator
- Removable waste container
- Folding safety element
- Cutting rollers are V-TEK by HSM with specially hardened steel rollers. This optimum design of all cutting unit components saves valuable energy
- Continuous motor operation
- Quiet Operation feature shreds documents with a pleasantly, quiet operating sound
- Anti-Jam Technology design to easily and quickly reverse out paper in the event that the machine is overloaded
- Optional: Automatic oiler for cross-cut and micro-cut ensures long time cutting performance and quality
- 13 gallon waste bag capacity; Part #HSM1408



| HSM part#                          | HSM1780               | HSM1781               | HSM1783                     | HSM1782               |
|------------------------------------|-----------------------|-----------------------|-----------------------------|-----------------------|
| Cutting type                       | Strip cut             | Strip cut             | Cross cut                   | Micro cut             |
| Cutting size                       | 1/8"                  | 1/4"                  | 3/16" x 1 1/8"              | 1/16" x 9/16"         |
| Security level DIN 32757-1         | 2                     | 2                     | 3                           | 4                     |
| Security level DIN 66399           | P-2 / O-2 / T-2 / E-2 | P-2 / O-2 / T-2 / E-2 | P-4 / O-3 / T-4 / E-3 / F-1 | P-5 / T-5 / E-4 / F-2 |
| Cutting capacity per run in sheets | 22 - 24               | 28 - 30               | 17 - 19                     | 11 - 13               |
| Cutting speed                      | 13 ft / min           | 13 ft / min           | 13 ft / min                 | 13 ft / min           |
| Throat opening                     | 9.5"                  | 9.5"                  | 9.5"                        | 9.5"                  |
| Motor at max. no. of sheets        | 500W                  | 500W                  | 500W                        | 500W                  |
| Motor power (horsepower)           | 0.67                  | 0.67                  | 0.67                        | 0.67                  |
| Voltage                            | 115 V/60 Hz.          | 115 V/60 Hz.          | 115 V/60 Hz.                | 115 V/60 Hz.          |
| Dimensions (H x W x D)             | 23.8" x 12.5" x 15.5" | 23.8" x 12.5" x 15.5" | 23.8" x 12.5" x 15.5"       | 23.8" x 12.5" x 15.5" |
| Weight                             | 40 lbs                | 40 lbs                | 45 lbs                      | 45 lbs                |
| Shred-bin volume                   | 9 gallons             | 9 gallons             | 9 gallons                   | 9 gallons             |
| Cutting capabilities               |                       |                       |                             |                       |

All technical specifications are approximate values. Technical and design modifications reserved.