


## Intense IR HD-TVI 1080p 2MP Indoor/Outdoor Bullet Cameras

- HT7040T** 2.8-12mm auto iris varifocal lens, dark grey housing  
**HT7041T** 3.6mm fixed lens, dark grey housing

### Features

- Full HD resolution over coax (HD-TVI)
- Supports up to Full HD 1080p @ 30fps
- True WDR operation
- Intense IR function – no saturation, IR intensity adapts to subject to provide vivid image
- True day/night operation – mechanical IR cut filter
- Heater circuitry and anti-moisture glass reduce fog or condensation under any weather condition
- 3-axis for wall and ceiling mounting
- Full OSD operation through on-board control and UTC (up the coax)
- 12VDC & 24VAC dual voltage operation
- Vandal / tamper resistant
- IP67 compliant
- 5 year warranty



### Camera Specifications

Image Sensor ..... 1/3" Sony Exmor CMOS, 2.0MP  
 Minimum Illumination..... 0.001 lux  
 Effective Pixels ..... 1984 (H) x 1105 (V)  
 Total Pixels ..... 2000 (H) x 1121 (V)  
 Scanning System..... Progressive  
 IR Range ..... 98 ft. (depending on scene reflection)  
 Intense IR ..... 0 – 20 (adjustable)  
 S/N Ratio ..... More than 50dB  
 Output Resolution..... 1920x1080 @ 30fps / 1280x720 @ 60fps  
 Video Output..... 1.0Vp-p / 75 Ohms  
 Electronic Shutter ..... Auto / Manual (1/30 – 1/30,000 sec.) / Flicker  
 WDR..... On (Low / Middle / High) / Off  
 Day / Night..... Auto / Color / BW / External  
 White Balance ..... Auto / AWB / AWC-Set / Manual  
 Brightness..... 0 – 20 (adjustable)  
 AGC..... 0 – 20 (adjustable)  
 Sense-up ..... 2x – 32x (adjustable)  
 Backlight..... BLC / HSBLC  
 Motion Detection..... On / Off (4 zones)

### Camera Specifications (continued)

Privacy Masking ..... On / Off (16 zones)  
 Mirror ..... On / Off  
 V-Flip ..... On / Off  
 Sharpness ..... 0 – 20 (adjustable)  
 Lens Shading..... On / Off  
 DNR..... Off / Low / Middle / High  
 Test Monitor Output ..... CVBS  
 Communication..... UTC (up the coax)

### Operating & Unit Specifications

Power ..... 12VDC / 24VAC dual voltage  
 (power supply not included)  
 Power Consumption ..... 12VDC, 720mA max. / 24VAC, 260mA max.  
 Operating Temperature..... -4°F – 140°F  
 Operating Humidity..... 20% - 95% RH  
 Unit Dimensions ..... 3.94" (W) x 3.94" (H) x 8.27" (L)  
 Unit Weight ..... 3.1 lbs.  
 Certifications..... FCC, RoHS

### Optional Accessories



**INTJBS**  
Square  
Junction Box



**INTCM**  
Corner/Pole  
Adaptor



**CVCJBB**  
Bullet Camera  
Junction Box



**PSW4**  
24VAC  
Power Supply



**PSW5**  
12VDC  
Power Supply



Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 3/16/15