


Intensifier® T HD-TVI 1080p 2MP Indoor/Outdoor Dome Camera

HTINT591T 3.6mm fixed lens, dark grey housing



Shown with included paintable, snap-on Chameleon Cover™

Features

- Full HD resolution over coax (HD-TVI)
- Supports up to Full HD 1080p @ 30fps
- True WDR operation
- Superior low-light performance
- Amplify existing light with no distance limitation
- With presets: Indoor, Outdoor, Low Light, Lobby, Elevator
- Heater circuitry and anti-moisture glass reduce fog or condensation under any weather condition
- 3-axis for wall and ceiling mounting
- Chameleon Cover™: snaps on and can be painted to match any décor!*
- Full OSD operation through on-board control and UTC (up the coax)
- 12VDC & 24VAC dual voltage operation
- Vandal / tamper resistant
- IP67 compliant
- 5 year warranty

Camera Specifications

Image Sensor 1/3" Sony Exmor CMOS, 2.0MP
 Minimum Illumination..... 0.001 lux
 Effective Pixels 1984 (H) x 1105 (V)
 Total Pixels 2000 (H) x 1121 (V)
 Scanning System..... Progressive
 S/N Ratio More than 50dB
 Output Resolution..... 1920x1080 @ 30fps / 1280x720 @ 60fps
 Video Output..... 1.0Vp-p / 75 Ohms
 Electronic Shutter Auto / Manual (1/30 – 1/30,000 sec.) / Flicker
 WDR..... On (Low / Middle / High) / Off
 Day / Night..... Auto / Color / BW / External
 White Balance Auto / AWB / AWC-Set / Manual
 Brightness..... 0 – 20 (adjustable)
 AGC..... 0 – 20 (adjustable)
 Sense-up 2x – 32x (adjustable)
 Backlight..... BLC / HSBLC
 Motion Detection..... On / Off (4 zones)
 Privacy Masking On / Off (16 zones)

Camera Specifications (continued)

Mirror On / Off
 V-Flip On / Off
 Sharpness 0 – 20 (adjustable)
 Lens Shading..... On / Off
 DNR..... Off / Low / Middle / High
 Test Monitor Output CVBS
 Communication..... UTC (up the coax)

Operating & Unit Specifications

Power 12VDC / 24VAC dual voltage
 (power supply not included)
 Power Consumption 12VDC, 500mA max. / 24VAC, 195mA max.
 Operating Temperature... -4° F – 140° F
 Operating Humidity..... 20% – 95% RH
 Unit Dimensions 3.35" (H) x 4.72" (Dia.)
 Unit Weight..... 2.2 lbs.
 Certifications..... FCC, RoHS

Optional Accessories



INTPM
Pendant Mount
(use with 59PLATE
and CVCJBD)



INTWM
Wall Mount
(use with 59PLATE
and CVCJBD)



CVCJBD
Dome Camera
Junction Box
(use with 59PLATE)



59PLATE
Adaptor Plate



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply



*Chameleon Cover™ - for best results when used outdoors, waterproof paint is recommended. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 3/17/15