

1080p HD-TVI Digital Video Recorder

D4VT	4 Channel 1080p HD-TVI Digital Video Recorder
D8VT	8 Channel 1080p HD-TVI Digital Video Recorder
D16VT	16 Channel 1080p HD-TVI Digital Video Recorder

Storage 1TB - 8TB

D4VT1TB	D8VT1TB	D16VT2TB
D4VT2TB	D8VT2TB	D16VT3TB
D4VT3TB	D8VT3TB	D16VT4TB
D4VT4TB	D8VT4TB	D16VT6TB
D4VT6TB	D8VT6TB	D16VT8TB
D4VT8TB	D8VT8TB	




Front panel



Rear panel

D4VT Shown



Features

EZ Wizards

- Setup: for quick system setup
- Network: network setup and portforwarding
- Record: quickly setup recording resolutions and recording type

EZ Search: quickly search events from thumbnails

EZ Copy: auto copy what you are playing onto a USB flash drive

- 1080p @ 15fps / 720p @ 30fps over coax (HD-TVI)
- Backwards compatible with all analog cameras
- UTC function allows for zoom/focus and OSD control over coax
- Video Out: 1 HDMI®, 1 VGA, 1 CVBS
- H.264 video compression
- Networkable DVR with free Speco DDNS server
- Digital Deterrent® supports up to 8 audio files for triggering during sensor or motion detection
- 2-way audio communication
- Built-in S.M.A.R.T. Technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- 4 channel audio recording
- Covert camera operation provides enhanced security and administrator control
- Password to secure installation authorization
- Switch between low and high quality stream during simultaneous Continuous + Motion or Continuous + Sensor recording modes for storage optimization

- Smart (Museum) Search - Quickly search for a specific video event without the need for motion setup.
- Easy firmware upgrade by USB port or network
- Instant and convenient backup via USB flash drive or network
- Supports multiple PC based browsers such as Internet Explorer, Google Chrome, Firefox and Safari
- Simultaneous playback/record while continuing to network transfer or backup
- User Access: up to 4 concurrent users for live viewing, 1 user for playback
- Remote monitoring / recording / playback / configuration / software upgrades and PTZ control via internet
- Network accessible via SpecoTech Multi-Client Software, SecureGuard™ Plus, Web-Viewer and Speco Player Mobile Viewer
- PC and MAC® compatible
- IR remote control and mouse included
- Digital watermarking
- 3 year warranty

Free Apps with support for view on most smart devices

iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 8/14/15



Optional Accessories



ERS1V
Vented Rack Shelf



IRRPTKIT
IR Repeater Kit

ITEM		D4VT	D8VT	D16VT	
Video	Input	Channel	4	8	16
		Input Level	Composite, 1.0Vp-p, 75 ohms		
		Signal Format	NTSC / PAL		
		Video Loss Check	Yes		
	Output	HDMI®	1 HDMI (1024x768, 1280x720, 1280x1024, 1920x1080)		
		VGA	1 VGA (1024x768, 1280x720, 1280x1024, 1920x1080)		
CVBS / Spot		1 main or 1 spot			
Audio	Input & Output		4 line input & 1 line output		
	Audio Codec		G.711		
Alarm	Sensor Input		4 channel (NC/NO selectable)		
	Alarm Output		1 alarm out by sensor, motion, video loss, HDD temperature and HDD failure		
Serial	RS-485	PTZ	1		
Recording	Compression		H.264		
	Multi-Operation		QUADPLEX (play / record / network / backup)		
	Resolution	1080p	60fps	120fps	240fps
		720p	120fps	240fps	480fps
		960H	120fps	240fps	480fps
	Recording Mode		Continuous / Schedule / Motion / Sensor / Manual / Continuous + Motion / Continuous + Sensor		
	Motion Detection		Motion detection setup by grid		
	Recording by Channel's Resolution		Yes		
	Pre-Recording		Max. 20 minutes		
Post Recording		Max. 60 seconds			
Playback	Multi-Decoding		1, 4	1, 4, 8	1, 4, 9, 16
	Search Mode		EZ Search, Smart (Museum) Search, Timeline, Event, Archive, Log		
Storage	HDD	Interface Type	Serial ATA		
		Capacity of 1 HDD	4 TB		
		Internal HDD	2		
	Backup	USB Flash Drive	Video & Still Image		
		USB External HDD	Video & Still Image		
		Network	Video & Still Image		
USB Port		1 front, 1 rear			
User I/F	Menu Display		GUI		
	Input Method		IR, Mouse, Keyboard Controller		
Network	Interface		10/100Base-T	10/100/1000Base-T	
	Streaming		CIF 15fps / channel max.		
Network Access	Mobile Viewer		Live, Search, PTZ, 2-Way Audio		
	PC Web Viewer		Internet Explorer, Chrome, Firefox, Safari (Live, Search, Backup, PTZ, Remote Setup)		
	PC Client		SpecoTech Multi-Client Viewer and SecureGuard® Plus CMS (Live, Search, Backup, PTZ, Remote Setup)		
	MAC Client		Speco Client for MAC and SecureGuard® CMS (Live, Search, Backup, PTZ, Remote Setup)		
Features	Digital Deterrent®		Default + up to 8 custom audio files		
	Digital Zoom		Yes		
	DLS (Daylight Savings)		Yes		
	EZ Record		Yes		
	S.M.A.R.T		Yes		
	Internal Beep		By video loss, HDD error		
	Multi-Language		English / Spanish / French		
	Dynamic DNS		Yes (free Speco DDNS)		
	SW Upgrade		USB and remote software upgrade		
	Email Notification		Yes		
NTP (Network Time Protocol)		Yes			
Power Source	Power Supply Voltage		12VDC, 3A	12VDC, 5A	
Allowable Operating Temperature / Humidity		41° F - 104° F / 20% - 80% RH			
Allowable Storage Temperature		14° F - 122° F			
Weight	Unit Weight (Gross Weight)		3.3 lbs.		
Dimensions	Unit Dimensions (W x H x D)		13.4" (W) x 2.48" (H) x 10.31" (D)		

Please note that specifications and unit exterior design are subject to change without notification.