

HSM[®] FP3000 Barrel Crusher

Robust and reliable



- Suited for pressing light metal and rolled hoop barrels
- Low height
- Small footprint
- Press ram with spikes for opening the barrels and collector tray for residual fluid
- Enclosed on all sides with inspection window for safety and dust reduction
- Membrane keypad with LED for operator safety
- Automatic return stroke saves time, overhead and personnel costs
- Low maintenance, durable eletro-hydraulics

HSM part#	HSM6820
Pressing Power	27.5 tons
Motor in Horsepower	10.05 hp
Voltage / Frequency	3 x 220V / 60 Hz
Barrel type	Light metal & rolled hoops / 55 gallon drums
Barrel size	24.3" x 42.9"
Hourly output	50 barrels
Cycle time in idle operation (theoretical)	33 sec
Machine Dimensions (H x W x D)	113.85" x 45.98" x 37.79"
Machine Weight	2138 lbs

All technical specifications are approximate values. Technical and design modifications reserved.