

## **4-port KVM switch with dual VGA - USB 2.0**

*StarTech ID: SV431DVGAU2A*



This USB KVM lets you connect four computers, each with dual VGA outputs, to a dual-monitor workstation. You can switch the workstation between each computer, as well as two additional USB peripheral devices and 3.5mm speakers & microphone.

### **Maximize productivity with dual video**

With support for two VGA video inputs and four different computers, this KVM switch maximizes productivity. Not only can you access multiple computers, but you can also use two VGA monitors on each computer streaming independent content to each display, which gives you the freedom to multitask and increase your productivity. The VGA ports support resolutions up to 1920x1200 for maximum screen viewing space.

### **Multi-system access**

Featuring dual video and support for your keyboard and mouse, along with a 2-port USB hub for additional peripheral devices, this KVM switch is perfect for accessing four separate systems using the same workstation. Support for your workstation plus two additional peripheral devices makes this KVM ideal for server control, simplifying access to multiple computer systems.

### **Hassle-free operation**

This 4-port KVM ensures effortless operation with intuitive hotkey control. It provides a simple yet comprehensive solution for switching between each connected computer and also supports manual operation using the easy-to-access buttons located on the front of the switch.

The SV431DVGAU2A is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Applications

- Control four computers, each with dual head video cards, to increase your productivity at the office
- Work with multimedia applications such as video & photo editing
- Operate multiple computers in manufacturing lines
- Install in your server room, for multi-computer access

## Features

- Maximum productivity with dual display and multi-computer access
- Hassle-free operation with hotkey and push-button switching
- Share your USB peripheral devices with built-in 2-port USB hub
- Supports resolutions up to 1920x1200
- 3.5mm speaker and microphone console support

## Technical Specifications

|                            |                                                    |
|----------------------------|----------------------------------------------------|
| Warranty                   | 2 Years                                            |
| Audio                      | Yes                                                |
| Cables Included            | No                                                 |
| Daisy-Chain                | No                                                 |
| KVM Ports                  | 4                                                  |
| Multi-Monitor              | Yes                                                |
| PC Interface               | USB                                                |
| PC Video Type              | VGA                                                |
| Rack-Mountable             | Optional                                           |
| DVI Support                | No                                                 |
| IP Control                 | No                                                 |
| Maximum Analog Resolutions | 1920 x 1200                                        |
| Maximum Number of Users    | 1                                                  |
| Port Selection Support     | Push Button and Hotkeys                            |
| Supported Resolutions      | up to 1920 x 1200                                  |
| Console Interface(s)       | 2 - VGA (15 pin; High Density D-Sub) Female Output |
| Console Interface(s)       | 1 - 3.5 mm Mini-Jack (3 Position) Female Output    |
| Console Interface(s)       | 4 - USB A (4 pin) Female                           |
| Host Connectors            | 8 - VGA (15 pin; High Density D-Sub) Female Input  |
| Host Connectors            | 8 - 3.5 mm Mini-Jack (3 Position) Female Input     |
| Host Connectors            | 4 - USB B (4 pin) Female                           |
| Color                      | Black                                              |
| Enclosure Type             | Steel                                              |
| Product Depth              | 5.1 in [130 mm]                                    |
| Product Height             | 2.4 in [60 mm]                                     |
| Product Length             | 6.4 in [163 mm]                                    |
| Product Weight             | 43.6 oz [1236 g]                                   |
| Product Width              | 8.7 in [220 mm]                                    |
| LED Indicators             | 1 - Green - Power                                  |
| LED Indicators             | 4 - Green - PC Detected                            |
| LED Indicators             | 4 - PC Selection Indicators                        |
| LED Indicators             | 4 - Red - PC Indicator                             |
| Center Tip Polarity        | Positive                                           |

|                           |                                                 |
|---------------------------|-------------------------------------------------|
| Input Current             | 0.8A                                            |
| Input Voltage             | 110 ~ 240 AC                                    |
| Output Current            | 1.5A                                            |
| Output Voltage            | 12 DC                                           |
| Plug Type                 | M                                               |
| Power Source              | AC Adapter Included                             |
| Humidity                  | 90% RH                                          |
| Operating Temperature     | 0°C to 40°C (32°F to 104°F)                     |
| Storage Temperature       | -20°C to 60°C (-4°F to 140°F)                   |
| Shipping (Package) Weight | 64.6 oz [1830 g]                                |
| Included in Package       | 1 - dual VGA USB KVM switch                     |
| Included in Package       | 1 - universal power adapter (NA / EU / UK / AU) |
| Included in Package       | 1 - instruction manual                          |

**Certifications, Reports and Compatibility**

