

Aura Professional™ Conference Phone

Affordable, Professional Conferencing Anywhere in the World



Do You Need A New Conferencing Phone?

Suppose you just upgraded to a larger conference room and now it fits fifteen people. Maybe you had a well-used conference phone that has finally stopped working. Well, you might be ready for a small business conference phone that has high quality, professional sound but is still affordable.

Choose the Aura Professional™

- It is full-duplex, which allows for simultaneous two way conversations
- Clear, natural sound made possible by wide band acoustic echo cancellation and dynamic noise suppression, as well as phone line echo suppression
- It comes with six microphones, four are internal and two external. With automatic, intelligent microphone mixing built in they can hear you well too

- You can store twenty numbers in the phone book, and speed dial twenty groups
- The 3 line LCD displays caller ID
- The 5 Watt speaker generates volume up to 90dB

This Conferencing Phone Has All You Need

This six (6) microphone conference phone comes with all you need for clear, full-duplex conversations. It automatically adjusts the phone circuitry so you can use it anywhere in the world. Everything you need to sound professional, without the high price tag!

Part	CP-3010
UPC	800807300378
MSRP	\$399.99

Aura Professional™ Conference Phone

Affordable, Professional Conferencing Anywhere in the World

Package Includes



Conferencing Phone



External microphones



Accessories

AC Adapter, Telephone Connectors, Power Box

Specifications

FEATURES

- Automatically adjusts phone circuit for the country it is being used in
- Full-duplex so all participants can speak and listen at the same time
- Wide band acoustic echo cancellation
- Dynamic noise suppression
- Automatic intelligent microphone mixing
- Echo cancellation eliminates **tunnel echo**
- Four Internal omni-directional microphones
- Two external microphones

TELEPHONE AND ELECTRICAL SPECIFICATIONS

- Telephone Connection:** Analog PBX or standard analog PSTN line
- Telephone connector:** Standard RJ-11
- Loudspeaker volume:** 90dB at 5 Watts, Bandwidth 200HZ- 3.3kHz
- Uni-directional Microphones:** -43 sensitivity
- Certifications:** FCC part 15 Class A, A-Tick, Canadian, UL, VCCI, RoHS

MECHANICAL SPECIFICATIONS

- Dimensions Phone:** 13.3"L & W x 2.5"H 33.8 x 6.3 cm
- External Microphone dim:** 3.9" x 1.6" (100mm x 40mm)
- Weight:** 1lb. 10 oz (740g)
- Package:** 14" x 14" x 4" (35.5cm x 35.5cm x 10.2cm)
- Package weight:** 4 lb. (1.9 kg) 2 external microphones
- Operating Temperature:** 32°F- 122°F (0°C - 50°C)

CONTROLS

- Microphone Mute
- Call Hold
- Redial and Flash buttons
- Volume up and down switches
- Standard keypad "0" through "9", * and # buttons
- Caller ID
- Ring volume adjust, 12 steps
- Menu
- OK (accept) button
- Green and Red microphone indicator LEDs