

## Cat6 Patch Cable - Shielded (SFTP) - 3m, Gray

*StarTech ID: N6SPAT3MGR*



This 3-meter Cat6 cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections. And the cable is shielded to protect your network against electromagnetic interference (EMI/RFI) and system noise to provide the perfect solution for fast and safe network connections.

### Reliable Cat 6 Gigabit connections

Constructed with 100% copper and foil shielded twisted-pair wiring, this cable was built for quality performance. The cable is designed to protect the data traveling through your network and is perfect in environments with a large amount of EMI. The results are faster speeds and improved data transmission.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

### Secured network connections

For easier cable runs, the snagless connectors protect the RJ45 clips during installation, making them less prone to snagging or breaking. This ensures a sturdy connection by preventing the cable from becoming loose from the plug.

Plus, the moulded boots offer strain relief that stops the RJ45 connector termination points from bending at sharp angles, which reduces the risk of damage to the cable that could decrease network performance.

The N6SPAT3MGR is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Applications

- Connect PoE-enabled devices to Gigabit networks
- Connect between computers, hubs, switches, print servers and patch panels
- Connect a workstation to an RJ45 wall outlet
- Deliver data, voice and video over Gigabit networks

## Features

- Protect your data against noise and EMI/RFI interference
- Prevent cable damage with moulded RJ45 connectors with strain relief
- Create secured connections with snagless clips that protect the connectors during installation

## Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	Shielded Snag-less
Fire Rating	CMG Rated (General Purpose)
Number of Conductors	4 Pair SFTP
Wiring Standard	TIA/EIA-568-B.1-2001 T568B
Cable Rating	CAT6 - 500 MHz
Connector A	1 - RJ-45 Male
Connector B	1 - RJ-45 Male
Cable Length	3 m [9.8 ft]
Color	Gray
Product Length	3 m [9.8 ft]
Product Weight	150 g [5.3 oz]
Wire Gauge	26 AWG
Package Quantity	1
Shipping (Package) Weight	160 g [5.6 oz]
Included in Package	1 - 3m Gray Cat6 Shielded (SFTP) Patch Cable

Certifications, Reports and Compatibility

