

HSM[®] SECURIO

B35 document shredder

Ideal for open-plan offices



- Ideal for small businesses; for 6 – 11 users
- Shreds staples, paper clips, credit/store cards, and CD/DVDs
- Integrated light barrier starts shredder automatically and switches it off after paper feed ends
- Anti-Jam Technology prevents jams when machines is overloaded
- Continuous Duty Operation ensures continual shredding with no down time
- High user safety guaranteed by the folding safety element which prevents unintentional intake
- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Comprehensive safety system – UL Approved, CE-certified
- Quiet operation while shredding
- Cutting cylinder made of 100% solid steel for high cutting capacities
- Multifunction button with reversing function
- Inspection window to monitor filling level
- Casters for mobility
- Additional options: PAPERcontrol function to measure paper thickness
- Automatic Oiler for cross-cut and micro-cut ensures long time cutting performance and quality
- 58 gallon waste bag capacity; Part #HSM2117



HSM part#	HSM1920	HSM1921	HSM 1923	HSM1922
Cutting type	Strip cut	Strip cut	Cross cut	Cross cut
Cutting size	1/8"	1/4"	3/16" x 1 1/8"	1/16" x 9/16"
Security level DIN 32757-1	2	2	3	4
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	30 - 32	40 - 42	24 - 26	16 - 18
Cutting speed	17 ft / min	17 ft / min	15.75 ft / min	15.75 ft / min
Throat opening	15.75"	15.75"	15.75"	15.75"
Motor at max. no. of sheets	590W	590W	590W	590W
Motor power (horsepower)	0.79	0.79	0.79	0.79
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"	34.25" x 24.3" x 20.67"
Weight	106.5 lbs	106.5 lbs	120 lbs	120 lbs
Shred-bin volume	34.3 gallons	34.3 gallons	34.3 gallons	34.3 gallons
Cutting capabilities				

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM[®]