


1000 TVL Day/Night Weather Resistant Color Bullet Camera / 63 IR LEDs

VL7038K 2.8-12mm auto iris varifocal lens, dark grey housing

Features

- 1/3" 1.3MP Sony Sensor
- 1000 TV lines of resolution
- True Day/Night compatibility
- Multi-mount is a unique mount allowing installers to manipulate the camera to almost every angle with simplicity
- Zero noise and no ghosting effect with digital noise reduction (DNR)
- External control rings for easy focus & distance adjustment
- Highest resolution: vivid, sharp picture in complete darkness
- 5 year warranty



Specifications


Image Sensor	1/3" 1.3MP Sony Sensor
Resolution	1000 TV lines
Minimum Illumination	0 lux (IR LED on)
Effective Pixels	1305 (H) x 1049 (V)
Total Pixels	1312 (H) x 1069 (V)
Number of IR LEDs	63
IR Range	164 ft. (depending on scene reflection)
IR LED Wavelength	850nm
White Balance	ATW / AWB / AWC-Set / Manual
S/N Ratio	More than 50dB (AGC off, weight on)
Backlight Compensation	HLC / BLC / Off / WDR
Electronic Shutter Speed	Auto / Manual / Flicker
OSD	Available
DNR	On / Off (level adjustable)
DWDR	On / Off
Sharpness	0-10' (level adjustable)
Privacy	On / Off (16 zones)
Scanning System	Progressive scan
Brightness	0-20 (level adjustable)

Synchronization	Internal
Day/Night	Color / BW / Auto / EXT
Motion Detection	On / Off (4 zones)
Sense-Up	Off / Auto
Mirror	On / Off
Digital Zoom	On (1x - 8x) / Off
Power Consumption	12VDC, 200mA (CDS off) 700mA (CDS on) 24VAC, 150mA (CDS off) 450mA (CDS on)
Power Supply	12VDC / 24VAC dual voltage operation (power supply not included)
Operating Temperature/ Humidity	- 4°F – 140°F / RH 95% max.
Storage Temperature/ Humidity	- 4°F – 140°F / RH 95% max.
Dimensions	5.31" (W) x 3.74" (H) x 11.57" (L)
Weight	4 lbs.

Optional Accessories



INTJBS
Square
Junction Box



INTCM
Corner/Pole
Adaptor



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply