





HL-L5200pw

The Brother HL-L5200DW monochrome laser printer is perfect for offices and small workgroups looking for quality and reliability. It delivers cost-efficient, two-sided output thanks to a high-yield replacement toner cartridge. Plus, it quickly prints high-quality business documents up to 42ppm. Use the 250-sheet capacity paper tray for letter or legal-size documents, and print envelopes and alternative media types from the 50-sheet capacity multi-purpose tray. For fewer refills, you can expand the paper capacity to 1,340 sheets with optional add-on trays. Easily share the printer on your wireless or Ethernet network and print with ease from a wide range of mobile devices. Advanced security features help protect your documents and device from unauthorized access.

Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	1-line LCD
Paper Size (maximum)	Paper Tray: Up to 8.5" x 14" (legal) Multi-Purpose Tray: 3.0" - 8.5" (W) / 5.0"-14" (L
Print Speed (maximum)	Up to 42ppm
Time to First Page▲	Less than 7.2 seconds
Print Resolution (maximum)	Up to 1200 x 1200 dpi
Processor	800 MHz
Emulations	PCL6, BR-Script3*, IBM Proprinter, Epson FX, PDI version 1.7, XPS Version 1.0
Duplex Printing Capability	Yes
Paper Input Capacity (maximum) [∞]	250-sheet capacity paper tray, 50-sheet capacity multi-purpose tray
Optional Input Capacity (max.*) [∞]	1,340 sheets via optional trays
Output Capacity (maximum) [∞]	150 sheets (face down), 1 sheet (face up)
Media Types	Plain Paper, Letterhead, Colored Paper, Recyclec Paper, Bond, Labels, Envelopes (up to 10)
Media Weights	Standard Paper Tray: 16 to 32 lbs. Multi-Purpose Tray: 16 to 53 lbs.
Memory (std. / max.)	256MB / 256MB
Standard Interfaces	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
Operating Systems Compatibility	Windows®: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista® / Windows® 7, 8, 8.1, 10 / Windows Server® 2003 / 2003 R2 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac® OS X® v10.8.5, 10.9.x, 10.10.x Linux
Mobile Device Compatibility [□]	AirPrint™, Google Cloud Print™ 2.0, Brother iPrint&Scan (free downloadable app), Cortado Workplace, Mopria®, Wi-Fi Direct®
Security Features	Secure Function Lock, Enterprise Security (802.1x), Lock Slot, Secure Print, SSL/TLS, IPSec
	(802.1X), LUCK SIOU, Secure FITHU, SSL/TLS, IFSec

Key Features at a Glance:

- Fast printing up to 42ppm
- Easily share with others via wireless or Ethernet networking
- · Automatic duplex (two-sided) printing
- Mobile device printing
- Flexible paper handling via 250-sheet capacity paper tray adjustable for letter or legal plus a 50-sheet capacity multi-purpose tray. Total capacity expandable to 1,340 sheets with optional add-on trays
- Cost-efficient output thanks to a high-yield 8,000-page replacement toner cartridge
- Restrict unauthorized printing and help protect sensitive documents with advanced security features
- Print professional business documents with bold, crisp text and sharp images
- 1 year limited warranty with free phone support for the life of your machine

Supplies & Accessories*:

TN-820	Standard Yield Toner Cartridge (approx. 3,000 pages) ▼
TN-850	High-Yield Toner Cartridge (approx. 8,000 pages) ▼
DR-820	Drum Unit (approx. 30,000 pages) [^]
LT-5500	Optional 250-Sheet Capacity Paper Tray
LT-6500	Optional 520-Sheet Capacity Paper Tray
BP60MPLTR	Multi-Purpose Paper (Letter, 500 sheets)

- PostScript®3™ compatible.
- Maximum capacity based on using 20 lb. paper. Additional purchase required.
- Requires connection to a wireless network. See www.connectprintshare.com for details, availability and mobile device compatibility.
- Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

 Approximately 30,000 pages based on 1 page per job and 50,000 pages based on 3 pages per job [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.

























