BUSINESS LASER PRINTER

For Offices and Small Workgroups









HL-L5200DWT

The Brother HL-L5200DWT monochrome laser printer is perfect for offices and small workgroups that need a reliable printer with a large paper capacity. It quickly prints high-quality documents up to 42ppm, and delivers cost-efficient, two-sided output thanks to a high-yield replacement toner cartridge. Reduce paper refills with dual paper trays (250-sheet and 520-sheet capacity), along with a 50-sheet capacity multipurpose tray for printing envelopes and alternative media. Plus, for even greater paper capacity add an optional add-on tray for a 1,340-sheet total capacity. Easily share the printer on your wireless or Ethernet network and print with ease from a wide range of mobile devices^{-.} Advanced security features help protect your sensitive documents and the printer from unauthorized access.

Specifications:

| Print Technology | Electrophotographic Laser |
|----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| LCD Display (type/size) | 1-line LCD |
| Paper Size (maximum) | Paper Tray: Up to 8.5″ x 14″ (legal) Multi-Purpose Tray: 3.0″ - 8.5″ (W) / 5.0″-14″ (L) |
| Print Speed (maximum) | Up to 42ppm |
| Time to First Page▲ | Less than 7.2 seconds |
| Print Resolution (maximum) | Up to 1200 x 1200 dpi |
| Processor | 800 MHz |
| Emulations | PCL6, BR-Script3*, IBM Proprinter, Epson FX, PDF version 1.7, XPS Version 1.0 |
| Duplex Printing Capability | Yes |
| Paper Input Capacity (maximum) [∞] | (1) 250-Sheet Capacity Paper Tray, (1) 520-Sheet Capacity Paper Tray, 50-Sheet Capacity Multi- Purpose Tray |
| Optional Input Capacity (max.*) [∞] | 1,340 sheets via optional tray |
| Output Capacity (maximum) [∞] | 150 sheets (face down), 1 sheet (face up) |
| Media Types | Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 10) |
| Media Weights | Standard Paper Tray: 16 to 32 lbs. Multi-Purpose Tray: 16 to 53 lbs. |
| Memory (std. / max.) | 256MB / 256MB |
| Standard Interfaces | Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0 |
| Operating Systems Compatibility | Windows®: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista® / Windows® 7, 8, 8.1, 10 / Windows Server® 2003 / 2003 R2 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac® OS X® v10.8.5, 10.9.x, 10.10.x Linux |
| Mobile Device Compatibility ^a | AirPrint™, Google Cloud Print™ 2.0, Brother iPrint&Scan (free downloadable app), Cortado Workplace, Mopria®, Wi-Fi Direct® |
| Security Features | Secure Function Lock, Enterprise Security (802.1x), Lock Slot, Secure Print, SSL/TLS, IPSec |
| | |

Yes

Mac

Key Features at a Glance:

- Fast printing up to 42ppm
- Easily share with others via wireless or Ethernet networking
- Automatic duplex (two-sided) printing
- Mobile device printing
- Flexible paper handling via dual paper trays (250-sheet and 520-sheet) adjustable for letter or legal plus a 50-sheet capacity multi-purpose tray. Total capacity expandable to 1,340 sheets with optional add-on tray
- Cost-efficient output thanks to a high-yield 8,000-page[▼] replacement toner cartridge
- Restrict unauthorized printing and help protect sensitive documents with advanced security features
- Print professional business documents with bold, crisp text and sharp images
- 1 year limited warranty with free phone support for the life of your machine

Supplies & Accessories^{*}:

| TN-820 | Standard Yield Toner Cartridge (approx. 3,000 pages)♥ |
|-----------|----------------------------------------------------------|
| TN-850 | High-Yield Toner Cartridge (approx. 8,000 pages)♥ |
| DR-820 | Drum Unit (approx. 30,000 pages) [^] |
| LT-5500 | Optional 250-Sheet Capacity Paper Tray |
| LT-6500 | Optional 520-Sheet Capacity Paper Tray |
| BP60MPLTR | Multi-Purpose Paper (Letter, 500 sheets) |
| | |

From ready mode and standard trav PostScript®3™ compatible.

ENERGY STAR® Qualified

Requires connection to a wireless network. See www.connectprintshare.com for details, availability and mobile device compatibility. Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

Maximum capacity based on using 20 lb. paper.

* Additional purchase required.

Approximately 30,000 pages based on 1 page per job and 50,000 pages based on 3 pages per job [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.











Join @BrotherOffice

otherearth.com

All trademarks and registered trademarks referenced herein are the property of their respective companies. Windows, Vista, Windows Vesta, Windows Server and the Windows logo are trademarks of Microsoft Corporation in the United States and/or other countries. Mac OS, the Mac logo, OS X, AirPrint and the AirPrint logo are trademarks of Apple Inc. registered in the U.S. and other countries. @2015 Google Inc. All rights reserved. Google Cloud Print is a trademark of Google Inc. Mopria and the Mopria logo are trademarks of Mopria Alliance, Inc. Cortado is a trademark of Cortado AG. All specifications are subject to change without notice. Images are for illustrative purposes only.