


Weather Resistant Long Range License Plate Capture Bullet Camera

CLPR67H 5-50mm F1.4 auto iris varifocal lens, black housing
IR-corrected lens with internal adjustments for zoom & focus

Note: Because of the special nature of this camera, during the day the scene will be monochrome. All license plates will be highlighted.

Features

- High-contrast imaging performance that delivers sharp, clear license-plate captures
- 8 pieces super high powered IR LEDs work perfectly even in total darkness to deliver clear license plate images
- 5-50mm varifocal IR-corrected lens optimizes day/night performance, even in very low light conditions and captures a wide field
- Captures license plates at up to 110 mph
- Weather resistant operation
- IP66 compliant
- 5 year warranty



Specifications

Image Sensor	1/3" 960H CCD
Resolution.....	700 TV lines
Minimum Illumination.....	0 lux (with IR LEDs on)
Effective Pixels	1020 (H) x 508 (V)
Type.....	Monochrome
Number of IR LEDs	8 pieces super high powered LEDs
IR Range	16.3 - 98.3 ft. (depending on scene reflection)
IR LED Wavelength	850nm
TV System.....	NTSC
Viewing Angle	Horizontal: 35° (wide) - 8° (tele) Vertical: 38° (wide) - 10° (tele)
S/N Ratio	More than 52db
Video Output.....	1.0Vp-p / 75 ohms
Scanning System.....	2:1 interlaced
Power Supply	12VDC (power supply included)
Power Consumption	1500mA (with inner heater and fan)
Operating Temperature.....	- 22° F – 140° F
Housing	Compact die cast aluminum sunshield
Dimensions.....	5.5" (Dia.) x 19.3" (L)
Weight	5.5 lbs.

