

V1200-P Zero Client for VMware and Amazon WorkSpaces TERA2 PCoIP® Portal Processor

Industry Leading VDI Performance

The 10ZiG V1200-P is part of our V1200 Tera2 PCoIP® Zero Client Series optimized for VMware and Amazon WorkSpaces environments. With no operating system and no local storage, the V1200 Series line provides an ultra-secure yet powerful and easy to manage endpoint that eliminates the chance of viruses and provides extensive USB security and authentication features. With options ranging from dual through quad screen, PoE, Fiber, DVI-I, DVI-D, 4 DisplayPort and Internal Smart Card (CAC) with up to 6 USB 2.0 ports as well as standard TAA Compliance on all V1200 Series Zero Clients, you can be confident in finding a device that will fit your ideal use case environment.


The V1200-P model highlighted below supports dual screens and comes equipped with 1 x DVI-D and 1 x DVI-I and 4 x USB 2.0, along with optional PoE and Fiber. All 10ZiG V1200 Series PCoIP® Zero Clients receive a one-year, free subscription to the Teradici Desktop Access Plan. The Desktop Access Plan includes the Teradici Management Console with a subscription to firmware and security updates as well as tech support.



▶ TERA2 PCoIP Portal Processor, Tera2321 PCoIP Chipset
▶ 1 x DVI-D + 1 x DVI-I
▶ 4 x USB 2.0
▶ Optional PoE
▶ Optional Fiber
▶ TAA Compliant
▶ Optional VESA Mount
▶ 1 year free subscription to Teradici Desktop Access Plan

V1200-P Zero Client

Tera2 PCoIP Zero Client Series



SPECIFICATIONS

1. Power On Indicator Light
2. Power Button
3. USB 2.0 (2)
4. Front Line Out
5. Mic In
6. USB 2.0 (2)
7. RJ45 LAN Port
8. DVI-D
9. DVI-I
10. Rear Line Out
11. DC Jack
12. Kensington Lock

System Specifications

Management Utility	Teradici Management
Form Factor	Slim Line
Processor	Teradici PCoIP® Portal Processor - TERA2
Chipset	TERA2321 PCoIP®

Dimensions

Device	5.12"(D) x 1.77"(W) x 5.91"(H) - 45mm x 150mm x 130mm
Weight	1.54 lbs (0.70 kg)

Connections

Ports	4 x USB 2.0, 1 x Mic In, 2 x Line Out, RJ-45 LAN, 1 x DC Jack
Video/Resolution	1 Monitor at 2560 x 1600* or 2 Monitors at 1920 x 1200, 1 x DVI-D + 1 x DVI-I

Networking

Ethernet	10/100/1000 Base-T
Fiber	Optional SFP Fiber Connector (100/1000Mbps)

Environmental

Operating Temp.	32-104F (0-40C), 10-90% non-condensing humidity
Power	7 Watts, DC-12V/3A External Power Adapter

Certifications

CE, FCC, CAN ICES-3/NMB-3, VCCI, UL, TUV-GS, C-Tick, GOST, BSMI, RoHS

* 1 x 2560 x 1600 requires the Hi-Res Video Cable (Part No: 9017)



Americas	P: +1 (866) 865-5250	E: info@10ZiG.com
EMEA	P: +44 (0) 116 214 8650	E: info@10ZiG.eu
APAC	P: +61 2 80027421	E: info@10ZiG.com.au
DE	P: +49(0) 6724 934-45	E: vertrieb@10zig.de

W: www.10ZiG.com

