

## HL274HPB

27" / 68,58 cm Diagonal LED-Backlight – Format 16:9



- 27" 16:9 LED Backlight Monitor
- 1920 x 1080 WUXGA Resolution
- Full HD Backlight Monitor
- 5ms Fast Response Time
- Triple Input: HDMI+DVI+VGA
- Built-In Stereo Speakers
- Tilt and Wall-Mountable (VESA)
- Low Power Consumption
- Multi-Video Modes
- ECO Friendly



# HL274HPB

27" / 68,58 cm Diagonal LED-Backlight – Format 16:9

**HANNING**  
by **HANNspree**

LCD Panel	Display Size	68,58cm / 27" Diagonal	
	Panel Type	LED-Backlight	
	Brightness	250 cd/m2	
	Contrast (Typical)	1000:1 (Typical)	
	Contrast (Active)	5M:1 (Active)	
	Pixel Pitch	0.311 (H) x 0.311 (V) mm	
	Resolution (H x V)	1920 x 1080	
	Aspect Ratio	16:9	
	Response Time	5 msec	
	View Angles LR, UD	H/V 170° / 160° (CR > 10)	
	Panel Surface	Anti-Glare	
	Display Colors	16.7M Colors	
	PC Input Range	Horizontal Freq.	30 to 80 kHz
		Vertical Freq.	60 to 75 Hz
Max. Display Freq.		1920 x 1080 @ 60Hz	
Interface	Input 1	D-Sub (VGA) x 1	
	Input 2	DVI-D x 1	
	Input 3	HDMI	
Output Terminal Power	Speakers	Yes, 2W x 2	
	Consumption	On:29W;Standby:<= 0.5W;Off:<=0.5W	
	AC Power Range	AC 100 ~ 240V, 50 ~ 60Hz	
	Power Mode Indicator	Power On: Green (LED) Power Saving: Green flicker (LED)	
Operating Condition	Temperature	5° ~ 35° C	
	Humidity	20% ~ 70%, non-condensing	
Physical	Dimensions	650 x 55 x 453 mm (W x D x H) TBC	
	Packing Dimens.	707 x 117 x 500 mm (W x D x H)	
	Net Weight	4,7 Kg	
	Gross Weight	6,3 Kg	

VESA Mounting	100 x 100 mm
Monitor stand	Regular Stand
Tilt	-5° ~ + 15°
Pivot	NA
Swivel	NA
Controls	Menu, Down, Up, Exit, Scale, Source, Power
Color	Warm, Cool, User Mode
Preset Mode	Movie, Photo, Game, Standard
On Screen Display	Languages: 9 OSD Languages
Carton Box	Brown Box
Accessory	Power Cable (1,5m), VGA Cable (1,5m) Warranty Card, Quick Start Guide (paper)

Contact Information

Actual products may differ slightly from those illustrated on this promotion material. Please refer to actual samples for final selection. The products displayed on this promotion material may not be available for purchase in your particular country or locality. Please check with your local Hannspree authorized representatives for the availability of specific products in your area. Hannspree reserves the right to alter design and specifications as well as to change the accessories with equivalents without notice.