

# Quam H16/SVPS

H16/SVPS is a horn assembly with a double re-entrant, compression horn with a 16W, 25/70V integrated transformer, and a square, stainless steel, vandal resistant, steel baffle. Mounting hardware is #8-32 'pin-in-torx.'



<b>APPLICATION</b>	<b>Intended Use:</b> <b>Program Material:</b> <b>Installation:</b>	Indoor or outdoor environment Paging and signal tones Horizontal or vertical surface mount
<b>AUDIO PERFORMANCE</b>	<b>Average Sensitivity:</b> <b>Loudspeaker Power Rating:</b> <b>Calculated Output:</b> <b>Magnet Type &amp; Weight:</b> <b>Frequency Response:</b> <b>Nominal Coverage Angle:</b> <b>Audio Connection:</b>	96dB SPL, 1W/1M 16W RMS, EIA 426A Standard 108dB SPL, 16W/1M BeFe Ceramic, 10 oz. Nominal 350Hz - 10kHz, EIA 426A Standard 90° Included Angle, -6dB/2kHz, Half Space 7", Color-coded, Pre-tinned Leads
<b>COMPONENT</b>	<b>Dimensions:</b> <b>Weight:</b> <b>Loudspeaker Model:</b> <b>Loudspeaker Specs:</b> <b>Transformer:</b> <b>Baffle:</b> <b>Finish:</b>	11 1/2" (H) x 11 1/2" (W) x 3 11/16" (D) 6 lbs. H16 8" O.D. loudspeaker 16W, 25/70V, with 5 taps (1W, 2W, 4W, 8W, 16W) BS8VPS: square, stainless steel White powder coat finish
<b>RECOMMENDED QUAM COMPONENTS</b>	<b>Surface Mount Enclosures:</b>	ES-8, ES8-6, SE1WVP, SE1WVPS, SE2WVP

