

# Product data sheet

Specifications



APC Smart-UPS On-Line, 3kVA, Tower, 208V, 2x L6-20R+1x L6-30R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit

SRT3000XLT

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Input Connection Type	NEMA L6-20P
output connection type	2 NEMA L6-20R 1 NEMA L6-30R
Cable length	10 ft (3.05 m)
Number of cables	1
Provided equipment	CD with software Documentation CD Installation guide Removable support feet USB cable Warranty card
Range of Product	Smart-UPS On-Line

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Type	Lead-Acid battery
Included Battery Modules	1
Typical recharge time	3 h
RBC Quantity	1
Battery Voltage	96V
Battery Charge Power (Watts)	165 W rated
Battery life	3...5 year(s)
Replacement battery	<a href="#">APCRBC152</a>

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Extendable Run Time	1
---------------------	---

## General

---

Topology	Double Conversion Online
----------	--------------------------

---

product web sub-family	High density
------------------------	--------------

---

Number of power module free slots	0
-----------------------------------	---

---

Number of power module filled slots	0
-------------------------------------	---

---

Redundant	No
-----------	----

## Physical

---

color	Black
-------	-------

---

Height	17.008 in (43.2 cm)
--------	---------------------

---

Width	3.3 in (8.5 cm)
-------	-----------------

---

Depth	25.0000000000 in (63.5 cm)
-------	----------------------------

---

Net Weight	69.005 lb(US) (31.3 kg)
------------	-------------------------

---

Mounting Location	Front
-------------------	-------

---

Mounting preference	Lower
---------------------	-------

---

Mounting Mode	Rack-mounted with kit
---------------	-----------------------

---

Two post mountable	0
--------------------	---

---

USB compatible	Yes
----------------	-----

---

Mounting position	Vertical
-------------------	----------

## Input

---

Input Frequency	40 - 70 Hz auto-sensing
-----------------	-------------------------

---

Efficiency at full load	100...275 V adjustable (half load)
-------------------------	------------------------------------

## Output

---

Maximum configurable power in VA	3000 VA
----------------------------------	---------

---

Max Configurable Power (Watts)	2700 W
--------------------------------	--------

---

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
----------------------------------	---------------------------------

---

Waveform Type	Sine wave
---------------	-----------

---

Harmonic distortion	Less than 2%
---------------------	--------------

---

Crest factor	3 : 1
--------------	-------

---

Bypass type	Internal Bypass (Automatic and Manual)
-------------	--

---

Additional information	Configurable for 208 or 240 nominal output voltage
------------------------	--

## Conformance

---

Product Certifications	ENERGY STAR V2.0 (USA)
------------------------	------------------------

## Environmental

---

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

---

Relative Humidity	0...95 % non-condensing
-------------------	-------------------------

Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Acoustic level	55 dBA
Online Thermal Dissipation	773 Btu/h
IP degree of protection	IP20

## Communications & Management

Free slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	340 J
---------------------	-------

## Ordering and shipping details

GTIN	731304317685
Country of origin	PH

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.7 in (24.6 cm)
Package 1 Width	34.3 in (87.1 cm)
Package 1 Length	23.6 in (59.9 cm)
Package 1 Weight	81.00 lb(US) (36.74 kg)

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)