

LOUDSPEAKERS: INFORMACAST® IP SPEAKER/CLOCKS

VALCOM

Valcom InformaCast® Compliant IP Speakers Enable Live, PreRecorded, Or Ad Hoc Audio Messages To Be Broadcast To Ten People Or Ten Thousand People — Instantly And Economically.

- PoE (802.3af) - No Local Power Required
- 2.5" Characters - 5 Character Display
- Clock Updates from Informacast Server
- Red LED's - Other LED Colors On Request
- Needs Only One Ethernet Port Connection
- Output Level 103 db/1Meter
- AUX Output Supports Valcom Amplified Speakers
- Optional Wall Volume Controls Available
- Mounting Backboxes Available
- Valcom Offers a Line of Stand Alone IP PoE Clocks, Visit www.valcomclocks.com



Backbox Selection Chart

IP SPEAKER/CLOCKS	ONE-WAY	TALKBACK	BACKBOX TYPE
A. IP Speaker Faceplate Unit w/Digital Clock White	VIP-419A-D-IC	VIP-429A-D-IC	22, 23, 24
B. IP Speaker Surface Mount w/Digital Clock Gray w/Black Grill	VIP-411A-DS-IC	VIP-431A-DS-IC	N/A
C. IP Speaker Faceplate Unit w/Digital Clock Gray w/Black Grille.	VIP-412A-DF-IC	VIP-432A-DF-IC	19
D. IP Speaker w/Analog Clock Gray		VIP-431A-A-IC	19, 20

Type	Part No.	Mount Style	Dimensions
19	VB-R19	Recessed	19.25\"H x 10.75\"W x 3.75\"D Grille Hole Dimns.: 10.00\" x 18.50\"
20	VB-S20	Surface	20.18\"H x 14.27\"W x 2.78\"D Grille Hole Dimns.: 10.50\" x 18.50\"
21	VB-A21 <i>Only works with Digital Clocks.</i>	Angled	19.88\"H x 14.27\"W x 5.50\"D ¹ x 2.71\"D ² Grille Hole Dimns.: 10.50\" x 18.50\"
22	VB-R22	Recessed	13.25\"H x 11.25\"W x 3.94\"D Grille Hole Dimns.: 10.50\" x 12.50\"
23	VB-S23	Surface	14.63\"H x 13.13\"W x 3.94\"D Grille Hole Dimns.: 10.50\" x 12.50\"
24	VB-A24	Angled	14.41\"H x 13.13\"W x 5.00\"D ¹ x 3.00\"D ² Grille Hole Dimns.: 10.50\" x 12.50\"

* One-Way/Talkback Programmable

800-825-2661 | Valcom.com | is@valcom.com | Roanoke, VA USA

InformaCast® is a Trademark of Singlewire Software.