


# 1000 TVL Color Indoor Dome Camera

**VL644K** 3.6mm fixed lens, black housing

**1000  
TVL**



## Features

- 1000 TV lines of resolution
- Easy installation & adjustment
- Compact & lightweight 3 axis design
- Manual 360° rotation & pan/tilt mechanism
- Low power consumption - max. 90mA
- 12VDC power supply required (power supply not included)
- Optional lenses available
- 5 year warranty

## Specifications

Image Sensor .....	1/3" Super High Resolution Image Sensor
Resolution.....	1000 TV lines
Minimum Illumination.....	0.001 lux @ F=1.2
Effective Pixels .....	1280 (H) x 960 (V)
Electronic Shutter .....	Auto (1/60 sec. - 1/100,000 sec.)
S/N Ratio .....	52dB
Backlight Compensation.....	Auto
Synchronization .....	Internal
Gamma.....	0.45 typ.
Video Signal Output.....	1.0Vp-p / 75 ohms
Operating Temperature/	
Humidity.....	14° F – 122° F / less than 80% RH
Storage Temperature.....	-4° F – 140° F
Power Consumption .....	90mA
Power Supply .....	12VDC (power supply not included)
Dimensions.....	4.7" (H) x 3.5" (Dia.)
Weight .....	10.5 oz.

## Optional Accessory



**PSW5**  
12VDC  
Power Supply

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/6/16