

MAN & MACHINE

# Really Cool

Medical Grade™

Terminally Cleanable Keyboards



Featuring

Tru-Lock



Washable at Workstation

Terminally



Withstands Submersion in 1:10 Bleach Solution

100% Quality



For Exceptional Return-on-Investment

Sani-Type



Great Tactile Feel Single or Double Gloved

Born-in-USA




Engineered, Manufactured & Serviced

# Really Cool Keyboard Details & Optional Private Labeling

**Optional Hospital Name & Logo Here**

**MAN & MACHINE**




Low profile keys make cleaning easier and a pleasure for typing




Fully sealed and seamless

Hygienic white keyboard lets you see bioburden



Cleaning instructions available on back



### Magfix

Magnets holds keyboard to tray for sanitary mounting. Optional mounting plates available for non-ferrous surfaces.

Optional



### Quick Disconnect Cable

Makes it easy to move keyboards from one location to another.

Optional



### Multi-Level Backlight

Allows light levels to be easily adjusted for any needed key illumination.

Optional

## Features

- Sealed, waterproof, immersible
- 100% Silicone rubber skin, no latex
- Tru-Lock - Keys lock for workstation disinfection
- May be terminally cleaned
- Quick disconnect available
- Excellent tactile feedback w/ gloves
- No moving parts, no mechanical failure
- Clean with any EPA-certified disinfectant
- Standard key pitch
- 2-year warranty w/ limited lifetime warranty available

## Specifications

- Weight: 1.7 lb (780 g)
- Size: 15 x 5.5 x 0.6 in (381 x 140 x 15.3 mm)
- Cable Length: 6 ft (1.83 m)
- Storage Temperature: -40° to 185°F (-40° to 85°C)
- Operating Temperature: 32° to 158°F (0° to 70°C)
- Power Consumption: 60mA (non-backlighted) 300mA (backlighted)
- Platform: Windows, Mac & Linux
- Layout: Includes numeric keypad and 12 Function keys
- IP 68
- Compliance: CE, FCC, EN-60601

## Color Choices



Hygienic White

Black

Isolation Workstation

Downtime Workstation

Dictation Workstation



info@mmimd.com  
www.man-machine.com  
(301) 341-4900

