

## SLP-102-TP

### PANEL MOUNT KEYBOARD WITH TOUCHPAD AND BACKLIGHTING



iKey's SlimKey™ SLP-102-TP panel mount keyboard provides full-size versatility in a rugged, compact design with the added convenience of an integrated touchpad. It features red LED backlit keys for use in areas with minimal lighting. Engineered for NEMA 4X protection against dust, water and corrosive liquids, the SlimKey™ SLP-102-TP is ideal for use in environments ranging from manufacturing to material handling to medical settings. Its large numeric pad allows for easy data entry, while its robust polycarbonate case protects it against any hazardous environment. Features: 10-Key Numeric Pad Industrial Silicone Rubber Keypad Integrated Backlighting Integrated Touchpad Lightweight ABS Polycarbonate™ Case Low-profile keys for easy cleaning MS Windows™ Function Keys

### Product Code SLP-102-TP

Certifications	NEMA 4X, CE UL60950, FCC Part 15 Class B
Shock	3x11 ns pulses of 50g on each of 3 axis
CABLE	10 feet (3 meters)
Key Switch	MATERIAL: Industrial Silicone Rubber LIFE: Greater than 10 Million Cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 7.05 oz. +/- 1.06 oz. (200g +/- 30g) FEEDBACK: Tactile with Mechanical Snap
Vibration	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2kHz DURATION OF TEST PER AXIS: 3 hours
Power	PS/2: KEYBOARD: 210mA@5V (from Keyboard port) TOUCHPAD: 10mA@5V (from Mouse port) USB: 220mA@5V (from CPU port)
Compatibility	KEYBOARD: PS/2: All Windows Operating Systems; USB: All Windows and Macintosh OS GLIDEPOINT: PS/2: All Windows Operating Systems; USB: All Windows and Macintosh OS
Temperature Range	STORAGE: -40C to +65C (-40F to +149F) OPERATING: 0C to 60C (+32F to +140F)
Weight	1.5 lbs (0.68 kg)
Warranty	1 Year Limited Warranty
Humidity	100% Humidity Resistant
Dimensions	15.10" x 6.05" x 0.58" (w-h-d) 383.5mm x 153.7mm x 14.7mm SCREWS: 0.50" (12.7mm) CUTOUT: 13.70" X 4.65" (w-h) 348mm x 118.1mm
Model Numbers	SLP-102-TP-PS2: With PS/2 cable SLP-102-TP-USB: With USB cable