



RETRACTABLE CABLE REEL 30' PAYOUT

FPSA/CR



Cable reel has 3 female plugs and a 30 foot retractable cable to accommodate any workspace. USA Plug NEMA 5-15

Max Rating - 10A, 125V, Indoor, Dry Location,
General Use Cord Reel Only

Tri-tap female outlet
Male plug - USA NEMA 5-15
Cable: 16 AWG/3C, 105C


Rating





RETRACTABLE CABLE REEL 30' PAYOUT

FPSA/CR





RETRACTABLE CABLE REEL 30' PAYOUT

FPSA/CR

PRODUCT SPECIFICATIONS	SHIPPING DIMENSIONS	
Length	292 mm	11.5 inch
Overall Height	267 mm	10.5 inch
Depth	140 mm	5.5 inch
Weight	3.63 kg	8 lbs
UPC Number	634878507158	

ELECTRICAL SPECS

Max Rating - 10A, 125V, Indoor, Dry Location,
General Use Cord Reel Only

Tri-tap female outlet
Male plug - USA NEMA 5-15
Cable: 16 AWG/3C, 105C

Rating

