



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Mini DisplayPort 1.2 to VGA Adapter Cable, Active, M/M, 6 ft. (1.83 m)

MODEL NUMBER: **P586-006-VGA-V2**

Converts a Mini DisplayPort v1.2 video signal for display on a VGA monitor, projector or television.

Features

Send High-Quality Mini DisplayPort v1.2 Video Signals to a VGA Display

- Connects Mini DisplayPort (or Thunderbolt) computer to VGA-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Mini DisplayPort and HD15 male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Integral strain relief for long life

Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Supports computer video resolution up to 1920 x 1200
- Supports HD video resolution up to 1920 x 1080 (1080p)
- No separate adapter required
- Nickel-plated connectors with gold-plated contact

Package Includes

- P586-006-VGA-V2 Mini DisplayPort 1.2 to VGA Active Adapter Cable, 6 ft.

Specifications

OVERVIEW	
UPC Code	037332191854
Technology	VGA/SVGA; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	5.0 +/- 15mm
Cable Jacket Rating	VW-1
Wire Gauge (AWG)	32



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Operating Humidity Range	0 to 85%, Non-Condensing
Storage Humidity Range	0 to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>