



PRODUCT FEATURES

- Exclusive noise-canceling microphone meets the highest standards to receive the coveted "6 Dragon" rating for speech accuracy by Nuance
- Pro-Flex wire microphone boom for perfect placement
- 40mm stereo speakers with deep bass sound deliver crystal clear audio
- Comfortable foam ear cushions
- Reversible for left or right side usage
- Stainless steel adjustable headband folds flat for storage
- Convenient in-line volume and mute controls
- Extra long 8-foot shielded cable with single 3.5mm plug for mobile use



PARAMETER	VALUE
Connections Microphone/Speaker Plug 3.5mm	Black
Microphone Noise Cancellation Frequency Range Electrical Signal-to-Noise Ratio Sensitivity at 1kHz (0dB=1V/Pa) Current Consumption	5dB/octave 100-10,000Hz >60dB -44dB <0.5mA
Speakers Frequency Range Coil Resistance Sound Output from 1kHz 1mW Input (0dB=20µPa) Maximum Input Power	50-20,000Hz 32 ohm 114dB 40mW

NC-181M

With 3.5mm single plug suitable for tablets, including iPad®, laptops including MacBook®, and most smartphones, including iPhone®



In-line Volume Control



Proprietary Microphone Design

